


Olympic Wire and Cable

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 9500, Computer, Low Capacitance Overall Foil Shielded Pairs RS-232, RS-422, RS-485 Cable



Computer, Low Capacitance Overall Foil Shielded Pairs RS-232, RS-422, RS-485 Cable

**Power Limited Circuit Cable-Class 2
24 Gage Stranded Conductors (7x32)**

Tinned Copper, Extruded insulated, Twisted pairs with overall Aluminum Mylar shield with stranded tinned copper drain wire, jacket

Applications:

Extruded insulated and paired for low capacitance for extended distance peripheral interconnection, approved for direct installation in air plenums without conduit, recommended for use up to 200 feet

Suggested Working Voltage:

150 volts maximum in accordance with NEC

SPECIFICATIONS

| | |
|----------------------------------|---|
| No. of Pairs | 2 |
| Conductor Size | 24 AWG |
| Stranding | 7/32 Tinned Copper |
| Insulation | Foamed FEP |
| Shielding | Overall Aluminum Mylar with Stranded Tinned Copper Drain Wire |
| Jacket | Low Smoke PVC, White |
| Nom. O.D. | 0.202 in |
| UL Style | CL2P, CMP |
| Nominal Capacitance ¹ | 12.2 pF/ft |
| Application | RS-232 RS-422 RS-485 |
| Color Code | Color Code Chart 11 |

RoHS Compliant



RoHS Compliant

1 Capacitance between conductors
