



**PIN RECEPTACLES**  
 for .015" - .020" diameter pins (#11 contact)  
 and .015" - .022" diameter pins (#21 contact)  
 (see specific contact range on page 217)



0548	8975	3016	9548
<b>0548-0-15-XX-21-XX-10-0</b> Solder mount in .036 min. mounting hole	<b>8975-0-15-XX-21-XX-10-0</b> Solder mount in .036 min. mounting hole	<b>3016-0-15-XX-21-XX-10-0</b> Solder mount in .036 min. mounting hole	<b>9548-0-15-XX-21-XX-10-0</b> Solder mount in .036 min. mounting hole

8637	1407	0553/8553															
		<table border="1" style="margin-top: 10px;"> <thead> <tr> <th>Basic Part Number</th> <th>Length L</th> <th>Depth N</th> </tr> </thead> <tbody> <tr> <td>0553-1</td> <td>.140</td> <td>.124</td> </tr> <tr> <td>0553-2</td> <td>.170</td> <td>.154</td> </tr> <tr> <td>0553-3</td> <td>.282</td> <td>.266</td> </tr> <tr> <td>8553-0</td> <td>.245</td> <td>.229</td> </tr> </tbody> </table>	Basic Part Number	Length L	Depth N	0553-1	.140	.124	0553-2	.170	.154	0553-3	.282	.266	8553-0	.245	.229
Basic Part Number	Length L	Depth N															
0553-1	.140	.124															
0553-2	.170	.154															
0553-3	.282	.266															
8553-0	.245	.229															
<b>8637-0-15-XX-21-XX-10-0</b> Solder mount in .037 min. mounting hole	<b>1407-0-15-XX-11-XX-10-0</b> Solder mount in .040 min. mounting hole	<b>X553-X-15-XX-X1-XX-10-0</b> Hex press-fit in .041 plated thru hole															

0566	0442	0554						
<table border="1" style="margin-top: 10px;"> <thead> <tr> <th>Basic Part Number</th> <th>Length L</th> </tr> </thead> <tbody> <tr> <td>0566-1</td> <td>.083</td> </tr> <tr> <td>0566-2</td> <td>.138</td> </tr> </tbody> </table>	Basic Part Number	Length L	0566-1	.083	0566-2	.138		
Basic Part Number	Length L							
0566-1	.083							
0566-2	.138							
<b>0566-X-15-XX-21-XX-10-0</b> Solder mount in .039 min. mounting hole	<b>0442-0-15-XX-11-XX-10-0</b> Solder mount in .040 min. mounting hole	<b>0554-0-15-XX-21-XX-10-0</b> Solder mount in .040 min. mounting hole						

<p><b>SPECIFICATIONS</b></p> <p><b>SHELL MATERIAL:</b> Brass Alloy 360, 1/2 Hard</p> <p><b>CONTACT MATERIAL:</b> Beryllium Copper Alloy 172, HT</p> <p><b>DIMENSION IN INCHES</b>  <b>TOLERANCES ON:</b>          LENGTHS: ±.005          DIAMETERS: ±.002          ANGLES: ± 2°</p>	<p><b>ORDER CODE: XXXX - X - 15 - XX - XX - XX - 10 - 0</b></p> <p><b>BASIC PART #</b> →</p> <p><b>SPECIFY SHELL FINISH:</b></p> <ul style="list-style-type: none"> <li>01 200µ" TIN/LEAD OVER NICKEL</li> <li>◇ 80 200µ" TIN OVER NICKEL (RoHS)</li> <li>◇ 15 10µ" GOLD OVER NICKEL (RoHS)</li> </ul> <p><b>SPECIFY CONTACT FINISH:</b></p> <ul style="list-style-type: none"> <li>02 100µ" TIN/LEAD OVER NICKEL</li> <li>◇ 84 100µ" TIN OVER NICKEL (RoHS)</li> <li>◇ 27 30µ" GOLD OVER NICKEL (RoHS)</li> </ul> <p><b>SELECT CONTACT</b>          #11 or #21 CONTACT (DATA ON PAGE 217)</p>
--	--