

0364	0363	0365	0366
<p><b>0364-0-15-XX-13-XX-10-0</b> Solder mount in .100 min. mounting hole Also available on 16mm wide carrier tape: 1,300 parts per 13" reel. Order as: 0364-0-57-XX-13-XX-10-0</p>	<p><b>0363-0-15-XX-23-XX-10-0</b> Solder mount in .102 min. mounting hole</p>	<p><b>0365-0-15-XX-23-XX-10-0</b> Hex press-fit in .105 plated thru hole</p>	<p><b>0366-0-15-XX-13-XX-10-0</b> Press-fit in .109 mounting hole</p>
0372	0362	0367	9324
<p><b>0372-0-15-XX-13-XX-10-0</b> Solder mount in .102 min. mounting hole Also available on 24mm wide carrier tape: 950 parts per 13" reel. Order as: 0372-0-57-XX-13-XX-10-0</p>	<p><b>0362-0-15-XX-X3-XX-10-0</b> Solder mount in .102 min. mounting hole</p>	<p><b>0367-0-15-XX-23-XX-10-0</b> Square press-fit in .040 plated thru hole</p>	<p><b>9324-0-15-XX-23-XX-04-0</b> Press-fit in .106 mounting hole</p>
0492	0381	4034	3044
<p><b>0492-0-15-XX-13-XX-04-0</b> Press-fit in .106 mounting hole</p>	<p><b>0381-0-15-XX-23-XX-10-0</b> Press-fit in .104 mounting hole</p>	<p><b>4034-0-15-XX-23-XX-04-0</b> Press-fit in .109 mounting hole</p>	<p><b>3044-0-15-XX-23-XX-04-0</b> Solder mount in .104 min. mounting hole</p>

**SPECIFICATIONS**

**SHELL MATERIAL:**  
Brass Alloy 360, 1/2 Hard

**CONTACT MATERIAL:**  
Beryllium Copper Alloy 172, HT

**DIMENSION IN INCHES**  
**TOLERANCES ON:**  
LENGTHS: ±.005  
DIAMETERS: ±.002  
ANGLES: ± 2°

**ORDER CODE: XXXX - X - 15 - XX - XX - XX - XX - 0**

**BASIC PART #**

**SPECIFY SHELL FINISH:**  
01 200µ" TIN/LEAD OVER NICKEL  
◇ 80 200µ" TIN OVER NICKEL (RoHS)  
◇ 15 10µ" GOLD OVER NICKEL (RoHS)

**SPECIFY CONTACT FINISH:**  
01 200µ" TIN/LEAD OVER NICKEL  
◇ 80 200µ" TIN OVER NICKEL (RoHS)  
◇ 27 30µ" GOLD OVER NICKEL (RoHS)



**SELECT CONTACT**

#13 or #23 CONTACT (DATA ON PAGE 226)