

SERPAC 072 (exploded isometric) -Click on image to show toolbar. Use I to Play/Pause Animation. -Left click and drag on image to move 3D model.





- a) Zoom in & out with center wheel.
- b) Pause at any moment to view and or print views.
- c) Change the views to ortho and section views if needed from the Views pull down menu.
- d) Explore options included in the tool bar like: Views, Transparency of model, Lighting type, etc.

PART NO.	DESCRIPTION (Included)	ACCSESSORIES (Optional)	
7-2	TOP	PART NO.	DESCRIPTION
07	BOTTOM	51	Non-skid Feet
6005	#4X3/8" Self tapping (6)	370	Prototype grid board
		470	Prototype clad board

Enclosure weight .37 lbs / 168 gm


- 1) Enclosure meets or exceeds IP40 and NEMA 1
- 2) Circuit Board drawings can be download at:

http://www.serpac.com/Accessories/CircuitBoard/drawings/370-470.pdf

3) All components are RoHS Compliant.

ALL DIMENSIONS ARE ± .010" 3/17/10 (1 of 2) 619 Commercial Ave. Covina, CA 91723 Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

SERPAC 072 (user print)



PART NO. DESCRIPTION PART NO. BOTTOM Non-skid Feet 51 6005 #4X3/8" self tapping (6) 370 Prototype grid board 470 Prototype clad board

Notes: Enclosure weight .37 lbs /168 gm 1) Enclosure meets or exceeds IP40 and NEMA 1

2) Circuit Board drawings can be download at:

http://www.serpac.com/Accessories/CircuitBoard/drawings/370-470.pdf

3) All components are RoHS Compliant.

ALL DIMENSIONS ARE ± .010" 3/17/10 (2 of 2) 619 Commercial Ave. Covina, CA 91723 Ph. (626) 331-0517 Fx. (626) 331-8584 www.serpac.com