



**PIN RECEPTACLES**  
 for .015" - .020" diameter pins (#11 contact)  
 and .015" - .022" diameter pins (#21 contact)  
 (see specific contact range on page 217)



<p><b>8467</b></p> <p><b>8467-0-15-XX-21-XX-04-0</b> Hex press-fit in .036 plated thru hole</p>	<p><b>6192</b></p> <p><b>6192-0-15-XX-21-XX-04-0</b> Square press-fit in .032 plated thru hole</p>	<p><b>9553</b></p> <p><b>9553-0-15-XX-X1-XX-04-0</b> Hex press-fit in .041 plated thru hole</p>	<p><b>5531</b></p> <p><b>5531-0-15-XX-21-XX-10-0</b> Hex press-fit in .041 plated thru hole</p>
---	--	---	---

<p><b>7553</b></p> <p><b>7553-0-15-XX-11-XX-10-0</b> Hex press-fit in .041 plated thru hole</p>	<p><b>9407</b></p> <p><b>9407-0-15-XX-11-XX-10-0</b> Solder mount in .040 min. mounting hole</p>	<p><b>9462</b></p> <p><b>9462-0-15-XX-21-XX-04-0</b> Hex press-fit in .043 plated thru hole</p>	<p><b>1147</b></p> <p><b>1147-0-18-XX-21-XX-10-0</b> Press-fit in .043 min. mounting hole Accepts wire sizes up to .014" Dia.</p>
---	--	---	---

<p><b>3061</b></p> <p><b>3061-0-19-XX-21-XX-10-0</b> Wire Crimp Termination. Accepts wire sizes 28 AWG Max. / 32 AWG Min.</p>	<p><b>0579</b></p> <p><b>0579-0-15-XX-X1-XX-10-0</b> Press-fit in .040 mounting hole</p>	<p><b>8874</b></p> <p><b>8874-0-15-XX-11-XX-10-0</b> Bottom entry Surface mount</p>	<p><b>0613</b></p> <p><b>0613-0-15-XX-21-XX-10-0</b> Press-fit in .047 mounting hole</p>
---	--	---	--

<p><b>SPECIFICATIONS</b></p> <p><b>SHELL MATERIAL:</b> Brass Alloy 360, 1/2 Hard</p> <p><b>CONTACT MATERIAL:</b> Beryllium Copper Alloy 172, HT</p> <p><b>DIMENSION IN INCHES</b>  <b>TOLERANCES ON:</b>      LENGTHS: ±.005      DIAMETERS: ±.002      ANGLES: ± 2°</p>	<p><b>ORDER CODE: XXXX - X - 1X - XX - XX - XX - XX - 0</b></p> <p><b>BASIC PART #</b> →</p> <p><b>SPECIFY SHELL FINISH:</b></p> <ul style="list-style-type: none"> <li>01 200µ" TIN/LEAD OVER NICKEL</li> <li>◇ 80 200µ" TIN OVER NICKEL (RoHS)</li> <li>◇ 15 10µ" GOLD OVER NICKEL (RoHS)</li> </ul> <p><b>SPECIFY CONTACT FINISH:</b></p> <ul style="list-style-type: none"> <li>02 100µ" TIN/LEAD OVER NICKEL</li> <li>◇ 84 100µ" TIN OVER NICKEL (RoHS)</li> <li>◇ 27 30µ" GOLD OVER NICKEL (RoHS)</li> </ul> <p><b>SELECT CONTACT</b>      #11 or #21 CONTACT (DATA ON PAGE 217)</p>
--	--