

2-1437535-9 Product Details



2-1437535-9

TE Internal Number: 2-1437535-9



SIP Sockets

[Not EU RoHS or ELV Compliant \(Find RoHS Compliant Alternates\)](#)

Product Highlights:

- 10 Positions
- Contact Style = Screw Machine
- Leg Style = Standard
- Beryllium Copper Contact Base Material
- Gold (30) Contact Plating, Mating Area, Material

[View all Features](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Leg Style = Standard • Sleeve Material = Brass • Breakaway Header = Yes <p>Termination Related Features:</p> <ul style="list-style-type: none"> • Termination Post Length (mm [in]) = 3.18 [0.125] <p>Body Related Features:</p> <ul style="list-style-type: none"> • Number of Positions = 10 • Sleeve Material Plating = Tin-Lead <p>Contact Related Features:</p> <ul style="list-style-type: none"> • Contact Style = Screw Machine • Contact Base Material = Beryllium Copper • Contact Plating, Mating Area, Material = Gold (30) 	<p>Housing Related Features:</p> <ul style="list-style-type: none"> • Housing Material = Thermoplastic - GF • UL Flammability Rating = UL 94V-0 <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = Not ELV/RoHS compliant • Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C <p>Other:</p> <ul style="list-style-type: none"> • Brand = AMP