


KRP-11DG-110 Product Details




KRP-11DG-110

TE Internal Number: 8-1393101-5



Industrial Relays (General Purpose)

 [Converted to EU RoHS but not ELV Compliant](#)
([Statement of Compliance](#))

Product Highlights:

- Relay Type = General Purpose
- Relay Style = General
- KRP Series
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 10 A

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [KRPA, KRP, KA, KR 5 to 10 Amp General Purpose Relay](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Schematic](#)
- [Wiring Diagram](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Type](#) = 8 Pin Octal-Style Plug

Electrical Characteristics:

- [Contact Current Rating \(A\)](#) = 10
- [Coil Resistance \(Ω\)](#) = 10000
- [Actuating System](#) = DC
- [Coil Power, Nominal \(W\)](#) = 1.20
- [Input Voltage \(VDC\)](#) = 110

Body Related Features:

- [Series](#) = KRP
- Polarized = No
- Enclosure Color = Clear
- Type = Ice Cube

Contact Related Features:

- Relay Type = General Purpose
- [Mounting Options](#) = Socket
- [Enclosure Type](#) = Enclosed
- FCC Part 68 Isolation = No
- [Contact Base Material](#) = Silver Cadmium Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 48.80 x 37.30 x 34.90 [1.922 x 1.469 x 1.375]
- Pin Configuration = Industry Standard
- Wiring Diagram = K-11

Configuration Related Features:

- Relay Style = General
- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- [Coil Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS/Not ELV Compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS not ELV directives
- Approved Standards = UL Recognized, CSA Certified

Other:

- Brand = Potter & Brumfield