

## MDR-135-1 Product Details



**MDR-135-1**

TE Internal Number: 1393139-7

 [Active](#)

### Rotary Relays

Not EU RoHS or ELV Compliant

#### Product Highlights:

- Contact - Arrangement = 4 Form C, 4PDT, 4 C/O
- DC Actuating System
- Input Voltage = 28 VDC
- Coil Current = .362 A
- Coil - Resistance = 76  $\Omega$

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Dimensional Drawing](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 28
- Coil Current (A) = 0.362
- Coil - Resistance ( $\Omega$ ) = 76
- Coil - Rated Power (W) = 10.00
- Insulation - Initial Dielectric Between Contacts and Coil (V) = 1308

#### Dimensions:

- Base Dimensions (mm [in]) = 66.68 x 66.68 [2.625 x 2.625]
- Height (mm [in]) = 79.50 [3.130]

#### Configuration Features:

- Contact - Arrangement = 4 Form C, 4PDT, 4 C/O
- Coil - Magnetic System = Non-Latching

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

#### Conditions for Usage:

- Temperature Range ( $^{\circ}\text{C}$ ) = 0 - 65

#### Other:

- Brand = Potter & Brumfield
- Comment = Small