

MDR-136-1 Product Details



MDR-136-1

TE Internal Number: 1393139-9

 Active

Rotary Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- Contact - Arrangement = 8 Form C, 8PDT, 8 C/O
- DC Actuating System
- Input Voltage = 28 VDC
- Coil Current = .362 A
- Coil - Resistance = 76 Ω

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Dimensional Drawing](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Electrical Characteristics:

- Actuating System = DC
- Input Voltage (VDC) = 28
- Coil Current (A) = 0.362
- Coil - Resistance (Ω) = 76
- Coil - Rated Power (W) = 10.00
- Insulation - Initial Dielectric Between Contacts and Coil (V) = 1308

Dimensions:

- Base Dimensions (mm [in]) = 66.68 x 66.68 [2.625 x 2.625]
- Height (mm [in]) = 89.70 [3.530]

Configuration Features:

- Contact - Arrangement = 8 Form C, 8PDT, 8 C/O
- Coil - Magnetic System = Non-Latching

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- Temperature Range ($^{\circ}\text{C}$) = 0 - 65

Other:

- Brand = Potter & Brumfield
- Comment = Small