



Economy Adhesive

All-Purpose Adhesive Spray **3505**

Introduction

This adhesive works extremely well on surfaces such as paper, cloth, cardboard, felt, foam rubber and most plastics and glass. Its high-solids content provides quick-tack ability. Web spray pattern covers larger areas quickly.

Features / Benefits

Water Resistant Non-Wrinkling 3-Way Valve

Chemical Components

Propane	(74-98-6)	<1.5%
Butane		
2-Proponone		
Hexane	(110-54-3)	

Environmental Policy

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Packaging and Availability

Economy Adhesive is available in the following sizes:

3505-11S 11 Ounce Aerosol

MATERIAL SAFETY DATA SHEET

Finished Product



MSDS Ref. No: 3505-A

Economy Adhesive

1. PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: Economy Adhesive

PRODUCT DESCRIPTION: Economy Adhesive

PRODUCT CODE: 3505-11S

MANUFACTURER

Techspray, L.P.

2. COMPOSITION / INFORMATION ON INGREDIENTS

Chemical Name	$\underline{\text{Wt.\%}}$	CAS#	EINECS#
Hexane	10 - 50	110-54-3	203-777-6
L.P.G.	2 - 20	68476-85-7	
Acetone	10 - 30	67-64-1	200-662-2
N-Butane	<5	106-97-8	

3. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

PHYSICAL APPEARANCE: Clear to amber, sticky resin.

POTENTIAL HEALTH EFFECTS

EYES: Liquid contact can cause irritation, which may be severe. **SKIN:** Prolonged or repeated contact may cause skin irritation.

INGESTION: Harmful if swallowed.

INHALATION: Prolonged or excessive inhalation may cause respiratory tract irritation.

SIGNS AND SYMPTOMS OF OVEREXPOSURE

EYES: Symptoms of overexposure include: stinging, tearing, redness and pain.

SKIN: May cause slight irritation.

INGESTION: Not a likely route of exposure.

4. FIRST AID MEASURES

EYES: Immediately flush eyes with plenty of water for at least 15 minutes. Get immediate medical attention.

SKIN: Wash with soap and water. Get medical attention if irritation develops or persists.

INGESTION: Ingestion is unlikely because of the physical properties and is not expected to be hazardous. Do not induce vomiting unless instructed to do so by a physician.

INHALATION: Remove to fresh air.

5. FIRE FIGHTING MEASURES

FLASHPOINT AND METHOD: -20°C (-4°F)CC

FLAMMABLE LIMITS: 1.8 % to 9.5 %

GENERAL HAZARD: Flammable Liquid. Can release vapors that form explosive mixtures at temperatures at or above the flash point.

EXTINGUISHING MEDIA: Use alcohol foam, carbon dioxide, or water spray when fighting fires involving this material.

HAZARDOUS COMBUSTION PRODUCTS: Smoke, fumes and oxides of carbon.

EXPLOSION HAZARDS: Vapors may form explosive mixture with air.

FIRE FIGHTING EQUIPMENT: As in any fire, wear self-contained breathing apparatus pressure-demand, (MSHA/NIOSH approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

SMALL SPILL: Avoid runoff into storm sewers and ditches which lead to waterways.

LARGE SPILL: -Implement cleanup procedures.

- -If in public area, keep public away and advise authorities.
- -Recover by pumping (use an explosion proof or hand pump) or with a suitable absorbent.

ENVIRONMENTAL PRECAUTIONS

WATER SPILL: This material is a water pollutant and should be prevented from contaminating soil or from entering sewage and drainage systems and bodies of water.

must be followed whenever workplace conditions warrant a respirator's use.

9. PHYSICAL AND CHEMICAL PROPERTIES

PHYSICAL STATE: Liquid

ODOR: Low odor. COLOR: Straw-colored. pH: Not Applicable

PERCENT VOLATILE: Not Applicable BOILING POINT: > 37.7°C (100°F) FREEZING POINT: 0°C (32°F) EVAPORATION RATE: >1 (H2O=1) SPECIFIC GRAVITY: 0.635 @ 25°C

VISCOSITY: Not Determined **(VOC):** 437 g/L (non-exempt VOC)

10. STABILITY AND REACTIVITY

STABLE: YES

HAZARDOUS POLYMERIZATION: NO

STABILITY: Stable under normal conditions.

HAZARDOUS DECOMPOSITION PRODUCTS: Carbon Dioxide and carbon Monoxide may form when heated to decomposition.

11. TOXICOLOGICAL INFORMATION

EYE EFFECTS: May be mildly irritating to eyes.

12. ECOLOGICAL INFORMATION

ENVIRONMENTAL DATA: There is limited information available on the environmental fate and effects of this material. The primary environmental concern for release is the impact on aquatic and terrestrial species. Due care should be taken to avoid the accidental release of this material into the environment.

ECOTOXICOLOGICAL INFORMATION: Rainbow trout LC50=5540 mg/L/96H, Static conditions, 11-13 degrees C, Fathead Minnow LC50=7280 - 8120 mg/L/96H Flow-through conditions, Bluegill LC50 = 8300 mg/L/96H

13. DISPOSAL CONSIDERATIONS

DISPOSAL METHOD: Federal, State, and Local laws governing disposal of materials can differ. Ensure

compliance with proper authorities before disposal.

GENERAL COMMENTS: Dispose of in a manner consistent with federal, state, and local regulations.

14. TRANSPORT INFORMATION

DOT (DEPARTMENT OF TRANSPORTATION)

PROPER SHIPPING NAME: CONSUMER COMMODITY ORM-D

TECHNICAL NAME: Mixed Aliphatic Hydrocarbons

PRIMARY HAZARD CLASS/DIVISION: No classification

AIR (ICAO/IATA)

PROPER SHIPPING NAME: CONSUMER COMMODITY ID8000

PRIMARY HAZARD CLASS/DIVISION: 9

UN/NA NUMBER: ID8000 PACKING GROUP: NA

VESSEL (IMO/IMDG)

PROPER SHIPPING NAME: AEROSOLS IN LIMITED QUANTITIES OF CLASS 2

PRIMARY HAZARD CLASS/DIVISION: 2.2

UN/NA NUMBER: 1950 PACKING GROUP: NA

15. REGULATORY INFORMATION

UNITED STATES

CERCLA (COMPREHENSIVE RESPONSE, COMPENSATION, AND LIABILITY ACT)

CERCLA REGULATORY: Acetone (67-64-1)

TSCA (TOXIC SUBSTANCE CONTROL ACT)

TSCA STATUS: All components of this product are either listed or exempt from listing in the TSCA inventory.

CANADA

DOMESTIC SUBSTANCE LIST (INVENTORY): All components of this product are listed on the Canadian DSL.

16. OTHER INFORMATION

APPROVED BY: Pierce A. Pillon **TITLE:** Chemist

PREPARED BY: Steve Cook

REVISION SUMMARY New MSDS