
MINI MCR-SL-UI-UI(-SP)

Configurable 3-Way Isolating Amplifier



Data Sheet

11/2004

Product Description

The configurable 3-way isolating amplifier MINI MCR-SL-UI-UI(-SP) is used to electrically isolate, condition, amplify, and filter analog signals.

On the input and output side, the standard signals 0...20 mA, 4...20 mA, 0...10 V, 2...10 V, 0...5 V or 1...5 V are available, electrically isolated.

The DIP switch accessible on the side of the housing allows the configuration of the input and output signal ranges.

The voltage supply (19.2...30 V DC) can either be provided via connecting terminal blocks "3"/"4" or "7"/"8" of the modules, or together, via the DIN rail bus connector (see Figure 5 on page 6). Please also observe "Power Supply" on page 7.

Features




Figure 1 Features

- 1 Input: Standard signals
- 2 Transparent cover
- 3 Potentiometer for adjustment
- 4 Groove for ZBF 6 Zack marker strip
- 5 Output: Standard signals
- 6 Supply voltage
- 7 Connection option for DIN rail bus connector
- 8 DIP switch S1
- 9 DIP switch S2
- 10 Universal snap-on foot for EN mounting rails

Technical Data

| General Data | | | |
|--|--|--|--|
| Supply voltage | 19.230 V DC | | |
| Current consumption | < 20 mA | | |
| Power consumption | < 450 mW | | |
| Transmission error | | | |
| With alignment | < 0.1% | | |
| Without alignment | < 0.4% | | |
| Temperature coefficient | | | |
| max. | < 0.01%/K | | |
| typ. | < 0.002%/K | | |
| Cut-off frequency | 100 Hz | | |
| Step response (1090 %) | 3.5 ms | | |
| Test voltage (input / output / supply) | 1.5 kV, 50 Hz, 1 min. | | |
| Ambient temperature range | | | |
| Operation | -20°C+65°C (-4°F149°F) | | |
| Storage | -40°C+85°C (-40°F185°F) | | |
| Dimensions (W x H x D) | 6.2 mm x 93.1 mm x 102.5 mm | | |
| | (0.244 in. x 3.665 in. x 4.035 in.) | | |
| Conductor cross section | 0.22.5 mm ² (AWG 2412) | | |
| Stripping length | | | |
| Screw connection | 12 mm | | |
| Spring-cage connection | 8 mm | | |
| Housing design | Polybutylenterephthalate PBT, green | | |
| Tests / Approvals | C € c FAL us | | |
| | PROCESS CONTROL EQUIPMENT FOR HAZARDOUS LOCATIONS | | |
| | LISTED 31ZN Class I Div 2 Groups A, B, C, D T5 | | |
| | A) This equipment is suitable for use in Class I, Division 2, Groups A, B, C and D or non-hazardous locations only. | | |
| | B) Warning - explosion hazard - substitution of components may impair suitability for Class 1, Division 2. | | |
| | C) Warning - explosion hazard - do not disconnect equipment unless power has been switched off or the area is known to be non-hazardous. | | |

| Input (see Figure 1, detail 1) | I _{IN} | U _{IN} |
|-----------------------------------|-----------------|-----------------|
| Input signal range (configurable) | 020 mA, 420 mA | 010 V, 210 V, |
| | | 05 V, 15 V |
| Max. input signal | 50 mA | 30 V |
| Input resistance | approx. 50 Ω | approx. 100 kΩ |

| Output (see Figure 1, detail 5) | I _{OUT} | U _{OUT} |
|------------------------------------|---|-----------------------|
| Output signal range (configurable) | 020 mA, 420 mA | 010 V, 210 V, |
| | | 05 V, 15 V |
| Load | < 500 Ω | ≥ 10 kΩ |
| Ripple | $<$ 20 mV _{ss} (500 Ω) | < 20 mV _{ss} |
| Max. output signal | 28 mA / 12.5 V | 12.5 V / 22 mA |

| Conformance With EMC Guideline 89/336/EEC And Low Voltage Directive 73/23/EEC | | | | | |
|---|-----------------------|--------------------------|--|--|--|
| Immunity to Interference According to EN 61000-6-2 ¹ | | | | | |
| Discharge of static electricity (ESD) | EN 61000-4-2 | Criterion B ² | | | |
| Electromagnetic HF field | EN 61000-4-3 | Criterion A ³ | | | |
| Fast transients (Burst) | EN 61000-4-4 | Criterion B ² | | | |
| Surge voltage capacities (Surge) | EN 61000-4-5 | Criterion B ² | | | |
| Conducted disturbance | EN 61000-4-6 | Criterion A ³ | | | |
| Noise Emission According to EN 50081-2 | | | | | |
| Noise emission of housing | EN 55011 ⁴ | Class A ⁵ | | | |

¹ EN 61000 corresponds to IEC 1000

² Criterion B: Temporary impairment to operational behavior that is corrected by the device itself.

³ Criterion A: Normal operating behavior within the defined limits.

⁴ EN 55011 corresponds to CISPR11

⁵ Class A: Area of application industry.

Ordering Data

| Description | Order Designation | Order No. | |
|--|-------------------------|------------|--|
| Configurable 3-way isolating amplifier Screw terminal block, preconfigured (see "Data Type Key") | MINI MCR-SL-UI-UI | 28 64 38 3 | |
| Configurable 3-way isolating amplifier Screw terminal block, standard configuration (see "Standard Configuration" on page 7) | MINI MCR-SL-UI-UI-NC | 28 64 15 0 | |
| Configurable 3-way isolating amplifier Spring-cage terminal block, preconfigured (see "Data Type Key") | MINI MCR-SL-UI-UI-SP | 28 64 71 0 | |
| Configurable 3-way isolating amplifier Spring-cage terminal block, standard configuration (see "Standard Configuration" on page 7) | MINI MCR-SL-UI-UI-SP-NC | 28 64 16 3 | |

Accessories

| Description | Order Designation | Order No. |
|--|--------------------------------|------------|
| DIN rail bus connectors | ME 6,2 TBUS-2 1,5/5-ST-3,81 GN | 28 69 72 8 |
| Power terminal block with screw connection | MINI MCR-SL-PTB | 28 64 13 4 |
| Power terminal block with spring-cage connection | MINI MCR-SL-PTB-SP | 28 64 14 7 |
| System power supply | MINI-SYS-PS-100-240AC/24DC/1,5 | 28 66 98 3 |

Data Type Key

| | Input Range | | | | |
|---|-------------|--------|--------------------------|--|--|
| MINI MCR-SL-UI-UI / MINI MCR-SL-UI-UI-SP / | 010 V | 020 mA | (Standard Configuration) | | |
| | 020 mA | 020 mA | | | |
| | 420 mA | 420 mA | | | |
| | 010 V | 010 V | | | |
| | 210 V | 210 V | | | |
| | 05 V | 05 V | | | |
| | 15 V | 15 V | _ | | |



Screw Connection




Figure 2 MINI MCR-SL-UI-UI MINI MCR-SL-UI-UI-NC

Spring-Cage Connection




Figure 3 MINI MCR-SL-UI-UI-SP MINI MCR-SL-UI-UI-SP-NC

Installation



The device may only be installed and put into operation by qualified personnel. The corresponding national regulations (e.g. VDE, DIN) must be observed.

The assignment of the connecting terminal blocks is shown in Figure 4.

Block Diagram




Figure 4 Block Diagram

The MINI Analog module can be snapped onto all 35 mm DIN rails corresponding to EN 60715.

Using DIN rail bus connector ME 6,2 TBUS-2 1,5/5-ST-3,81 GN (Order No.: 28 69 72 8)



Please also pay particular attention to the direction of the MINI Analog module and DIN rail bus connector when snapping into position:

Snap-on foot (Figure 5, detail D 10) below and plug (Figure 5, detail C 11) left!

 First position the DIN rail bus connector in the DIN rail to bridge the voltage supply (see Figure 5).




Figure 5 Mounting/Removing

Power Supply



Never connect the supply voltage directly to the DIN rail bus connector!

It is not permitted to draw power from the DIN rail bus connector or from individual MINI Analog modules!

Feeding in power via the MINI Analog module

Where the total current consumption of the aligned MINI Analog modules does not exceed 400 mA, the power can be fed in directly at the connecting terminal blocks of a MINI Analog module. We recommend connecting a 400 mA fuse upstream.

Feeding in power with a power terminal block

Power terminal block MINI MCR-SL-PTB (Order No.: 28 64 13 4) of the same shape, or MINI MCR-SL-PTB-SP (Order No.: 28 64 14 7) is used to feed in the supply voltage to the DIN rail bus connector. We recommend connecting a 2 A fuse upstream.

Feeding in the power with a system power supply unit

System power supply unit MINI-SYS-PS-... (Order No.: 28 66 98 3) with 1.5 A output current contacts the DIN rail bus connector with the supply voltage, allowing several MINI Analog modules to be supplied from the network.

Configuration



Electrostatic Discharge!

The module contains components that can be damaged or destroyed by electrostatic discharge. When handling the module, observe the necessary safety precautions against electrostatic discharge (ESD), in accordance with EN 61340-5-1 and EN 61340-5-2, as well as IEC 61340-5-1 and IEC 61340-5-2.

DIP switches S1 and S2 (see Figure 1, details 8 and 9) are used to define the combination of input and output standard signal ranges (see "Configuration Table" on page 8).

Standard Configuration

If it is an "**NC version**" (MINI MCR-SL-UI-UI-NC or MINI MCR-SL-UI-UI-SP-NC), the device has the following standard configuration:

- Input 0...10 V,
- Output 0...20 mA,
- All DIP switches in the "off" position,
- Transmission error < 0.1%.

Configuration Table

| l _ | | DIP S2 | | | | ווט ן ן | P S1 | |
|-----------|----------------|--------------|-----|-----|-----|---------|------|-----|
| | UT 1 | 2 | 3 | 4 | 5 | 6 | 1 | 2 |
| | 20 mA off | | off | off | off | off | off | off |
| | 20 mA off | | off | off | off | ON | off | off |
| | 10 V ON | | ON | off | off | off | off | off |
| | 10 V ON | | ON | off | off | ON | off | off |
| | .5 V ON | | off | off | off | off | off | off |
| 1 | .5 V ON | 1 ON | off | off | off | ON | off | off |
| 210 V 02 | 20 mA off | off | off | ON | ON | off | off | off |
| 42 | 20 mA off | off | off | off | off | off | off | off |
| 0 | 10 V ON | l off | ON | ON | ON | off | off | off |
| | 10 V ON | l off | ON | off | off | off | off | off |
| 0 | .5 V ON | 1 ON | off | ON | ON | off | off | off |
| 1 | .5 V ON | 1 ON | off | off | off | off | off | off |
| 05 V 02 | 20 mA off | off | off | off | off | off | ON | off |
| | 20 mA off | | off | off | off | ON | ON | off |
| | 10 V ON | l off | ON | off | off | off | ON | off |
| 2 | 10 V ON | l off | ON | off | off | ON | ON | off |
| | .5 V ON | | off | off | off | off | ON | off |
| 1 | .5 V ON | 1 ON | off | off | off | ON | ON | off |
| 15 V 02 | 20 mA off | off | off | ON | ON | off | ON | off |
| | 20 mA off | | off | off | off | off | ON | off |
| | 10 V ON | l off | ON | ON | ON | off | ON | off |
| | 10 V ON | l off | ON | off | off | off | ON | off |
| 0 | .5 V ON | 1 ON | off | ON | ON | off | ON | off |
| 1 | .5 V ON | 1 ON | off | off | off | off | ON | off |
| | 20 mA off | off | off | off | off | off | off | ON |
| | 20 mA off | off | off | off | off | ON | off | ON |
| 0 | 10 V ON | l off | ON | off | off | off | off | ON |
| 2 | 10 V ON | l off | ON | off | off | ON | off | ON |
| 0 | .5 V ON | 1 ON | off | off | off | off | off | ON |
| 1 | .5 V ON | 1 ON | off | off | off | ON | off | ON |
| 420 mA 02 | 20 mA off | off | off | ON | ON | off | off | ON |
| | 20 mA off | off | off | off | off | off | off | ON |
| | 10 V ON | | ON | ON | ON | off | off | ON |
| | 10 V ON | | ON | off | off | off | off | ON |
| | .5 V ON | 1 ON | off | ON | ON | off | off | ON |
| 1 | .5 V ON | I ON | off | off | off | off | off | ON |

Alignment

Below the transparent cover is a potentiometer (see Figure 1, detail 3), with which a fine adjustment of the analog signals can be carried out after the configuration of the DIP switches has been altered.



The transmission error without adjustment is < 0.4%. Using the potentiometer, the error can be adjusted to < 0.1%.



Make sure you always use the latest documentation. It can be downloaded at www.download.phoenixcontact.com.

PHOENIX CONTACT Inc. P.O. Box 4100 Harrisburg, PA 17111-0100 USA



717-944-1300



717-944-1625



www.phoenixcon.com



info@phoenixcon.com