


8058-39G3 Product Details



8058-39G3
(3-1437508-6)

TE Internal Number: 3-1437508-6

 Active

Transistor Sockets and Adapters

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Socket
- Terminal Style = Printed Circuit
- Terminal Configuration = Contact
- Lead Size Accepted = .41 mm
- 8 Terminals

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Socket
- Terminal Configuration = Contact
- Product Series = 8058 Series
- Package = TO-5
- Sleeve Material = Brass
- Profile = Low

Termination Features:

- Terminal Plating = Gold

Dimensions:

- Lead Length Accepted (mm [in]) = 3.96 - 5.54 [0.156 - 0.218]
- Post Diameter (mm [in]) = 0.51 [0.020]
- Pin Circle Diameter (mm [in]) = 5.08 [0.200]

Body Features:

- Terminal Style = Printed Circuit
- Sleeve Material Plating = Gold
- Socket Type = Transistor
- Terminal Material = Beryllium Copper
- Insulator Material = Fluoropolymer

Configuration Features:

- Number of Terminals = 8

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Environmental:

- Operating Temperature (°C) = -55 - +125

Conditions for Usage:

- Lead Size Accepted (mm [in]) = 0.41 [0.016]

Other:

- Brand = AMP