DC Voltage




- Full 3-1/2 Digit, Bright Red 0.56" (14.2mm) Display
- Broad Range Display Scaling
- Short 2.94" (74.7mm) Deep, 1/8 DIN Case
- Screw Terminal Connector for Easy Installation
- Four User-Settable Ranges: 200mV, 2V, 20V, 200V
- One Factory-Settable Range: 750V
- Jumper-Selectable Decimal Point
- Optional Isolated 9-32VDC Power Supply
- Optional Excitation Output of 12VDC or 24VDC


The Falcon Series digital indicators are premium quality 1/8 DIN meters for industrial applications. All Falcon units feature jumper selectable decimal point (internal and on the connector for remote decimal point) and display scaling, providing wide application flexibility. In addition, signal input ranges are easy to change with jumpers on the main board. The Falcon has a 0.56" bright red LED display for high visibility.



Compactly designed for applications requiring minimal rear panel depth, the Falcon fits a standard 1/8 DIN panel cutout (92mm x 45mm) and requires less than 3" behind the panel. A screw terminal connector is a standard feature for easy wiring of the power supply and signal input connections.

Installation and Panel Cutout





Mounting Requirements

The Falcon series 1/8 DIN indicators require a panel cutout of 1.77" (45mm) high by 3.62" (92mm) wide. To install the Falcon into a panel cutout, remove the clips from the side of the meter. Slide the meter through your panel cutout, then slide the mounting clips back on the meter. Press evenly to ensure a proper fit.

Engineering Label Placement

If replacement of the engineering unit label is required, place the tip of a ball-point pen into the small hole at the base of the engineering label in the bezel. Slide the label up until it pops out. Grasp and remove. Slide the new label half the distance in, then use the ball-point pen to slide it down into place.

Specifications _____

DISPLAY

Type: 7-segment, red LED Height: 0.56" (14.2mm) Decimal Point: 3-position programmable, internally or on the terminal block Overrange indication: most significant digit = "1"; other digits blank Polarity: Automatic, with "-" indication, "+" indication implied

POWER REQUIREMENTS

AC Voltages: 120 or 220VAC, ±10%, 50/60Hz **DC Voltages:** 9-32VDC, ±1% **Power Consumption:** 3VA

ACCURACY @25º C

 $\pm 0.1\%$ of reading ± 1 count 750 ± 2 counts

ENVIRONMENTAL

Operating Temperature: 0 to 55°C Storage Temperature: -10 to 60°C Relative Humidity: 0 to 85% non-condensing Temperature Coefficient: (±0.01% of input ± 0.05 count)/°C Warm-up Time: Less than 15 minutes Response Time: Less than 1 second

NOISE REJECTION

NMRR: 50dB, 50/60Hz **CMRR:** (with 1KΩ unbalanced @ 60Hz): 90dB min.

ANALOG TO DIGITAL CONVERSION

Technique: Dual slope integration **Rate:** 3 samples per second, nominal


MECHANICAL

Bezel: 3.79"x 1.89" x .44" (96 x 48 x11.2mm) Depth: 2.94" (74.7mm) Panel Cutout: 3.6" X 1.77" (91.9 x 45mm 1/8 DIN) Case Material: 94V-1, UL rated Noryl® Weight: 9.0oz (255.1g)

INPUTS: DC Voltage

Input	Display	Input	Maximum		
Range	Resolution	Impedance	Overload		
200mV	100µV	\geq 100M Ω	50V		
2V	1mV	10MΩ	100V		
20V	10mV	10MΩ	100V		
200V	100mV	10MΩ	250V		

Wiring Diagram -



Input Signal: Connect the signal to be monitored to the IN HI and IN LO terminals. IN HI is terminal #1, IN LO is terminal #2.

Supply Power: Connect the supply power to terminals #11 and #12. Note that if AC power is supplied, terminal #11 is for Neutral, and terminal #12 is for Hot. If DC power is used, terminal #11 is for -DC, and #12 is for +DC.

Display Hold: This feature allows you to hold the displayed value indefinitely. A remote switch can be used to make the connection. To activate the display hold, short terminal blocks #3 and #4 (Hold Ref and +Ref). This connection must be kept isolated from other circuitry. To hold multiple units, separate poles of the switch must be used to maintain the isolation.



These instruments are designed for maximum safety to the operator when mounted in a panel according to instructions. They are not to be used unmounted or for exploratory measurements in unknown circuits.



Before switching the instrument on, make sure the supply voltage matches the power source required of the instrument as indicated on the hook-up label affixed to the instrument.


Decimal Point Selection -

From terminal block: The decimal point can be set from the rear screw terminal block by connecting the appropriate decimal point (DP 1, 2, 3,) to the DP C terminal. The J105 jumper must be in the D position (see diagram under "From front panel").

Decimal

Decimai													
Point	Connect	_1_	2	3	4	5	6	7	8	9	10	11 1	2
1.999	DP C to DP1					Ē	2	<u>س</u>					
19.99	DP C to DP2	ž	Z	55	Ë	Ы	DP	DP	DP	ХЩ	ΰŰ	202	
199.9	DP C to DP3		=	ΞĻ	+				-	+	θÅ	₹ † ∢	. +
1999	No Decimal												_

From front panel: The decimal point can also be selected by removing the front bezel from the meter. Move the push-on jumper J105 across the correct letter.



Voltage Range Selection


All Falcon Indicators are configured initially per the customer specifications. Range changes can be accomplished as follows:

Disconnect power from the unit. Remove the unit from the panel. Remove the front bezel by inserting slotted screwdriver in the vertical slots on either side of the bezel and then turning to pry the bezel off. Unscrew the two Phillips head screws at either side of the circuit board. Finally, push on the green connector assembly in the back of the unit to slide the main circuit board out from the meter. Change jumpers according to the chart below.

Note: If a new range is selected, the calibration procedure must also be performed.

pe benon	neu.								
	Input	J103	J106	JU101	JU102				
	Range								
	200mV	С	R	V	Yes				
	2V	A	R	V	No				
	20V	В	R	V	No	See Chart			
	200V	D	R	V	No	<			
* 750 volt range may be configured by factory or Simpson Authorized Service Center only									

Note: JU101 and JU102 are hard wire jumpers, and are removed by cutting them. Resoldering the JU jumpers is not recommended. If this is required, or if a function is to be changed (from volts to current), Simpson recommends returning the Falcon to the factory or an Authorized Service Center. After moving the jumpers to the desired location, put the Falcon back together and install in your panel, or proceed to calibration.




Application Example

A manufacturing plant requires a low cost digital meter to replace an analog panel meter on a 150VDC motor. The upgrade is required because the operator requires a display hold feature that is not available on the analog model.

A Falcon 3-1/2 digit indicator (200DCV) can fit this application. The meter needs no additional scaling before being installed into the panel. A switch is required for the display hold option. as one is not supplied by Simpson.

The meter is installed in parallel with the motor like the analog meter, and is ready to be placed in the panel.


The Falcon is less than 3" deep, fitting well into the restricted panel space. It will take up about as much space as the analog meter it replaced. In addition, display hold is a stan-



Falcon 200VDC


dard feature on the Falcon. By shorting connections #3 and #4, the operator can hold the display to take a reading, and then remove the short to reactivate the indication mode.

A switch can be used to short the connections. The meter is shipped ready to install, keeping down-time to a minimum.




Accessories -

Switchboard



Portable



External shunts enable DC volt digital panel meters to indicate higher DC currents than can be provided with self contained internal shunt meters. The shunt is installed in series with the load and the source. The shunts provide a DCmV drop which is sent to the display unit. The Falcon can be scaled to display the current between the load and the source. Simpson offers portable and switchboard shunts.

Each shunt includes 5' leads $(0.065\Omega$ resistance). Accuracy is within $\pm 1\%$ of rating.

Portable Shunts (50 mV)* Catalog Catalog Jumper Range of Amp Voltage Voltage Amp Drop Across R114 Readout Number Drop Number 50mV 1.00 06700 50mV 06500 1 Yes 5 50mV Yes 5.00 06706 150 50mV 06503 10 50mV 10.0 06704 200 50mV 06504 Yes 06705 50mV Yes 15 15.0 250 50mV 06505 20 50 mV Yes 20.0 N/A 300 50mV 06506 25 50mV Yes 25.0 06707 400 50mV 06507 30 50mV None 30.0 06708 500 50mV 06508 50 50mV None 50.0 06709 75 50mV None 75.0 06711 A portable or switchboard 100 50mV 100 06713 Yes shunt should be used with 150 50mV Yes 150 06714 Falcon series 200 mVDC 200 50mV Yes 200 06715 meters. Specifications can 10 100mV Yes 10.0 06716 30 100mV Yes 30.0 N/A be found on data sheet for 100mV None 100.0 06717 100 DC Voltage. 200 100mV Yes 200 N/A 10 200mV Yes 10.00 N/A **All switchboard shunts 200mV 20.0 20 Yes N/A require a jumper across R114. 100 200mV Yes 100.0 N/A

199.9

N/A

200mV

200

None

Ordering Information

Switchboard (50 mV)**