




Have a Question?
Chat with a Product Information Specialist

What can we help you find?

- [Products](#)
- [Industries](#)
- [Resources](#)
- [About TE](#)
- [My Account](#)
- [Innovation](#)
- [Support Center](#)

8060-1G6 Product Details

- [Share](#)
- [Print](#)
- [Email](#)



Transistor Sockets and Adapters

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Socket
- Terminal Style = Solder Pocket
- Terminal Configuration = Contact
- Lead Size Accepted = .41 mm
- 4 Terminals

[View all Features](#)

Quick Links

- [▶ Check Pricing & Availability](#)
- [▶ Search for Tooling](#)
- [▶ Product Feature Selector](#)
- [▶ Contact Us About This Product](#)

8060-1G6
(2-1437504-1)
TE Internal Number: 2-1437504-1
 Active

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> • None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> • Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> • Product Type = Socket • Terminal Configuration = Contact • Product Series = 8060 Series • Package = TO-5 • Sleeve Material = Brass • Profile = Low <p>Termination Features:</p> <ul style="list-style-type: none"> • Terminal Plating = Gold <p>Dimensions:</p> <ul style="list-style-type: none"> • Lead Length Accepted (mm [in]) = 3.96 - 5.54 [0.156 - 0.218] • Pin Circle Diameter (mm [in]) = 2.54 [0.100] <p>Body Features:</p> <ul style="list-style-type: none"> • Terminal Style = Solder Pocket • Sleeve Material Plating = Gold • Socket Type = Transistor • Terminal Material = Beryllium Copper • Insulator Material = Fluoropolymer 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Number of Terminals = 4 <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 240°C • RoHS/ELV Compliance History = Always was RoHS compliant <p>Environmental:</p> <ul style="list-style-type: none"> • Operating Temperature (°C) = -55 - +125 <p>Conditions for Usage:</p> <ul style="list-style-type: none"> • Lead Size Accepted (mm [in]) = 0.41 [0.016] <p>Other:</p> <ul style="list-style-type: none"> • Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference Products](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

[Privacy Policy](#)

Keep Me Informed

Receive TE News, Events &
Technology Updates

Enter your email address

