



Silver Line Series – Single & Multi-Output Linears





The Silver Line series follows the industry accepted footprint for open frame, linear power supplies. Sola improves on this design by offering standard screw terminal connections and optional covers for safety considerations.

Features

- · Easy-to-install screw terminal connections
- Cover options
- Industry standard footprint
- Universal input and approvals (115/230 VAC)
- Low noise, extremely quiet DC output. For noise sensitive or analog circuitry.
- Fast transient response. Ideal for test applications.
- Built-in OVP on 5 V models and optional on 12, 15 and 24 V models
- · Automatic resetting overload protection
- · Short circuit protected
- Two year warranty

Applications

- · Industrial control circuits and components
- Instrumentation
- Drives
- CNC machinery
- · Equipment for food industry
- Microprocessor circuits
- Analog circuits
- · Noise sensitive circuitry and sensors

Specifications

Parameter	Condition	Limit						
	Input							
Input Voltage	•	100/120/220/230/240 VAC Selectable						
Input Frequency		47-63 Hz						
	Output							
Line Regulation	for 10% change	0.05%						
Load Regulation	for 50% change	0.05%						
Ripple		3.0 mV maximum Peak-to-Peak						
DC Output Adjustment Range		±5% Minimum						
Overvoltage Protection		All 5-Volt outputs include build-in OVP as standard (setting is $6.2 \vee \pm 0.4 \vee$) OVP is optionally available on other types						
Transient Response Time	at 50% Load Changes	50 msec.						
Overload Protection		Automatic current limit foldback						
Remote Sensing	Available to compensate for output voltage drop on selected models.	0.5 VDC						
	General							
Operating Temperature Range	Derate to 40% at +70°C	0 to +50°C						
Storage Temperature Range		-25°C to +85°C						
Temperature Coefficient (Typical)		0.01% 0°C						
Stability	After warm-up	±.5%						
Vibration	Method 514	Per MIL-STD-810C						
Shock	Method 516	Per MIL-STD-810C						
EMI/RFI	Linear power supplies have inherently low conducted and radiate noise levels	For most system applications they will meet requirements of FCC Class B and VDE 0871 for class B						
Cover Option	Derate power by	an additional 15%						
Cooling	Forced air. 20 CFM required for full rating Derate 30% without cooling							

Specifications are typical. Load Regulation on outputs without Remote Sense, .1% typical.

SL Series Selection Table

Catalog Number	Output 1 Output 2		Output 3	Case
SLS-05-030-1T	5 V @ 3 A*#	_	_	A
SLS-05-060-1T	5 V @ 6 A*#	_	_	В
SLS-05-090-1T	5 V @ 9 A*#	_	_	С
SLS-05-120-1T	5 V @ 12 A*#	-	-	12
SLS12-017T1	12 V @ 1.7 A# or 15 V @ 1.5 A	_	_	А
SLS-12-034T	12 V @ 3.4 A#	-	-	В
SLS-12-051T	12 V @ 5.1 A#	-	-	С
SLS-12-068T	12 V @ 6.8 A#	-	-	12
SLS-15-045T	15 V @ 4.5 A#	-	-	С
SLS-15-060T	15 V @ 6 A#	-	-	12
SLS-24-012T	24 V @ 1.2 A#	-	-	Α
SLS-24-024T	24 V @ 2.4 A#	-	-	В
SLS-24-036T	24 V @ 3.6 A#	-	-	С
SLS-24-048T	24 V @ 4.8 A# –		_	12
SLS-24-072T	24 V @ 7.2 A#	-	-	к
SLS-24-120T	24 V @ 12.0 A#	-	-	L
SLD12-1010-12T1	12 V @ 1 A or 15 V @ .8 A	-12 V @ 1 A or -15 V @ .8	_	H1
SLD12-1818-12T ¹	12 V @ 1.8 A or 15 V @ 1.5 A	-12 V @ 1.8 A or -15 V @ – 1.5 A –		D
SLD-12-3434-12T	12 V @ 3.4 A#	12 V @ 3.4 A# -12 V @ 3.4 A#		13
SLD-15-3030-15T	15 V @ 3 A#	-15 V @ 3 A#	-	13
SLD-12-6034-05T	5 V @ 6 A*#	12 V @ 3.4 A#	-	11
SLD-12-3015-05T	5 V @ 3 A*#	12 V@ 1.5 A	-	C1
SLT12-20404-12T1	5 V @ 2 A*#	12 V @ .4 A or 15 V @ .4 A	-12 V @ .4 A or -15 V @ .4 A	H2
SLT12-31010-12T1	5 V @ 3 A*#	12 V @ 1 A# or 15 V @ .8 A	-12 V @ 1 A# or -15 V @ .8 A	F
SLT12-61010-12T1	5V @ 6 A*#	12 V @ 1 A or 15 V @ 1 A	-12 V @ 1 A or -15 V @ 1 A	14
SLT12-61818-12T ¹	5V @ 6A*#	12 V @1.8 A or 15 V @1.5 A -12 V @ 1.8 A or -15 V @ 1.5 A		G2
SLT24-30530-05T	5V @ 3A*	-5 V @ .5 A*	24 V @ 3 A	G1
Over Voltage Protect	ctor (OVP)			
SLO-12-000-1	6.2 V to 34 V Adjustable @ 8 A	For Cases B through K		J1
SLO-12-000-TB	6.2 V to 34 V Adjustable @ 8 A	For Case A or Cases B through K (when used with a cover)		J2


Notes:

* With Built-In OVP


With Remote Sense (R.S.)

 $^{\rm 1}$ 12/15 Volt models are factory set for 12 Volt operation. 15 Volt operation is field adjustable.

Dimensions - inches (mm)



Case A





Cover Options

Catalog Number	Description	Catalog Number	Description
SLCASA-CVR	Cover for Case A	SLCASG-CVR	Cover for Cases G1 and G2
SLCASB-CVR	Cover for Case B	SLCASH-CVR	Cover for Cases H1 and H2
SLCASC-CVR	Cover for Case C	SLCASI-CVR	Cover for Cases I1, I2, I3 and I4
SLCASC1-CVR	Cover for Case C1	SLCASK-CVR	Cover for Case K
SLCASD-CVR	Cover for Case D	SLCASL-CVR	Cover for Case L
SLCASF-CVR	Cover for Case F		


Note:

Covers are sold separately. When used, derate the power supply by 15% of its rated value.


Visit our website at www.solaheviduty.com or Contact **Technical Services** at **(800) 377-4384** with any questions.



Silver Line Dimensions (inches/mm)




Cases C and C1




Case D


AC Input Jumper Connections


AC Input Jumper Connections					
For use at:	100 VAC	120 VAC	220 VAC	230/240 VAC	
Connect:	1-3, 2-4	1-3, 2-4	2-3	2-3	
Apply AC:	1 & 5	1 & 4	1 & 5	1 & 4	



Case F








Cases H1 and H2

Visit our website at www.solaheviduty.com or contact **Technical Services** at **(800) 377-4384** with any questions.



Silver Line Dimensions (inches/mm)




Cases I1, I2, I3 and I4

Notes:


All dimensions in inches (mm). Dimensions may change and should not be used for construction purposes.

Be sure to specify the complete part number when ordering. Orders may be placed with your local Sola/Hevi-Duty distributor.




Case J1

Case J2



Case K



Case L

Visit our website at www.solaheviduty.com or Contact **Technical Services** at **(800) 377-4384** with any questions.