219 Series - Industrial Relays DPDT, 4PDT, 6PST, 10 Amps



Versatile. Rugged. Proven. These are but a few words used by customers to describe the 219 series. When long life and cost of down time / service are important the 219 solves the problem. It's a standard throughout industrial applications which many other relays are measured against. Capable of up to four poles double throw or six poles single throw. Contact arrangements are easily customized for special applications. NUCLEAR versions available.

GENERAL SPECIFICATIONS (@ 25° C)

Contacts:

Contact Configuration Silver Alloy-Gold Diffused **Contact Material** Contact Rating 120 / 240VAC Resistive

10 Amp / 5 Amp 28VDC Resistive 10 Amp 50 milliohms max @ 6vdc Contact Resistance, Initial

Coil:

Coils Available Nominal Coil Power Input Voltage Tolerance - AC Input Voltage Tolerance - DC Drop-out voltge Duty

AC and DC AC 5VA DC 1.8-2.5W 85% to 110% of nominal 80% to 110% of nominal 10% of nominal Continuous

Upto 4PDT or 6PST

Timing:

25 mS Operate Time (max) 20 mS Release Time (max)

Dielectric Strength:

500Vrms **Across Open Contacts** 1500Vrms Between mutally insulated point 10,000 Mohms min @ 500VDC Insulation resistance

Temperature:

 $AC = -20 \text{ to } 60^{\circ}\text{C} \text{ (-4 to } 140^{\circ}\text{F)}$ Operating $DC = -20 \text{ to } 70^{\circ}\text{C} (-4 \text{ to } 158^{\circ}\text{F})$ Storage -40 to 105°C (-40 to 221°F)

Life Expectancy:


100,000 Electrical (full load) 10,000,000 Mechanical (no load)

Miscellaneous:

Any Mounting Position Enclosure Clear Polycarbonate Weight 8.5oz (241 grams)



General Purpose Relays



Voltage	Make	Carry	Resistive	Inductive			
120VAC	30 Amp	10 Amp	10 Amp	3 Amp			
240VAC	30 Amp	10 Amp	5 Amp	1 Amp			
24VDC	30 Amp	10 Amp	10 Amp	5 Amp			
28VDC	30 Amp	10 Amp	10 Amp	3 Amp			
125VDC	30 Amp	10 Amp	0.5 Amp	0.1 Amp			
For versions with suffix "69" permant magnet blowouts							
Voltage	Make	Carry	Resistive	Inductive			
125VDC (SM)	30 Amp	10 Amp	1.5 Amp	0.5 Amp			
125VDC (DM)	30 Amp	10 Amp	4 Amp	1.5 Amp			
250VDC (SM)	30 Amp	10 Amp	0.5 Amp	150 mAmp			
250VDC (DM)	30 Amp	10 Amp	1.5 Amp	0.5 Amp			

Note: SM = Single make DM = Double make

Coil voltages and frequencies must be specified

219 Coil Specifications

AC Coils	C Coils, 50/60HZDC Coils_											
Nominal	Resistance	Milliar	npers	pers Impedance Nominal Resistance				Milliampers				
voltage	ohms	Cold	Hot	ohms	voltage	ohms	Cold	Hot				
	±10%					±10%						
6	1.1	1500	840	7.2	6	15.5	385	304				
12	4.2	750	410	27	12	63.5	189	147				
24	15.5	375	200	120	24/28*	250	96	77				
120	540	75	40	2,700	32	375	86	62				
240	2100	32	17	13,400	48	975	49	39				
-	-	-	-	-	115/125*	6200	20	16				
-	-	-	-	-	250	12400	20	16				

Note: Stock 24VDC and 115VAC relays have nameplates stamped 24/28VDC and 115/125VDC respectively. These relays operate at 80% of the lower voltages and operate within allowable temperature rises at higher voltages.

219 Series - Industrial Relays DPDT, 4PDT, 6PST, 10 Amps

Outline Dimensions

Dimensions Shown in inches & (millimeters)

12 Pin Plug-in

14 Pin Plug-in

0.25 (6.3)

3.04 (77.4)

2.58 (65.7)

1.45 (36.8)

