



NTE5304 thru NTE5307 Silicon Bridge Rectifier, 1.5A

Features:

- High Reverse Voltage to 1000V
- Surge Overload Ratings to 50A (Peak)
- Good for PC Board Assembly

Maximum Ratings and Electrical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified. Single Phase, Half Wave, 60Hz, Resistive or Inductive Load, Note 1.)

Maximum Recurrent Peak Reverse Voltage, V_{RRM}	
NTE5304	400V
NTE5305	600V
NTE5306	800V
NTE5307	1000V
Maximum RMS Bridge Input Voltage, V_{RMS}	
NTE5304	280V
NTE5305	420V
NTE5306	560V
NTE5307	700V
Maximum DC Blocking Voltage, V_{DC}	
NTE5304	400V
NTE5305	600V
NTE5306	800V
NTE5307	1000V
Maximum Average Forward Output Current ($T_A = +25^\circ\text{C}$), $I_{O(AV)}$	
1.5A	
Peak Forward Surge Current (8.3ms single half wave superimposed on rated load), I_{FSM}	
50A	
Maximum Forward Voltage Drop (Per element at 1A), V_F	
1.0V	
Maximum Reverse Current at Rated DC Blocking Voltage Per Element, I_R	
$T_A = +25^\circ\text{C}$	10 μ A
$T_A = +100^\circ\text{C}$	1mA
Operating Temperature Range, T_J	
-55° to +125°C	
Storage Temperature Range, T_{stg}	
-55° to +150°C	

Note 1. For capacitive load, derate current by 20%.

