



NTE251 (NPN) & NTE252 (PNP) Silicon Complementary Transistors Darlington Power Amplifier

Description:

The NTE251 (NPN) and NTE252 (PNP) are silicon complementary Darlington transistors in a TO3 type case designed for general-purpose amplifier and low-frequency switching applications.

Features:

- High DC Current Gain @ $I_C = 10A$:
 $h_{FE} = 2400$ Typ (NTE251)
 $h_{FE} = 4000$ Typ (NTE252)
- Collector-Emitter Sustaining Voltage: $V_{CEO(sus)} = 100V$ Min
- Monolithic Construction with Built-In Base-Emitter Shunt Resistors

Absolute Maximum Ratings: ($T_A = +25^\circ C$ unless otherwise specified)

| | |
|--|-------------------------------|
| Collector-Emitter Voltage, V_{CEO} | 100V |
| Collector-Base Voltage, V_{CB} | 100V |
| Emitter-Base Voltage, V_{EB} | 5V |
| Collector Current, I_C | |
| Continuous | 20A |
| Peak | 40A |
| Base Current, I_B | 500mA |
| Total Power Dissipation ($T_C = +25^\circ C$), P_D | 160W |
| Derate Above $25^\circ C$ | 0.915W/ $^\circ C$ |
| Operating Junction Temperature Range, T_J | -65° to $+200^\circ C$ |
| Storage Temperature Range, T_{stg} | -65° to $+200^\circ C$ |
| Thermal Resistance, Junction-to-Case, R_{thJC} | 1.09 $^\circ C/W$ |

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

| Parameter | Symbol | Test Conditions | Min | Typ | Max | Unit |
|---|----------------|---|-----|-----|-------|------|
| OFF Characteristics | | | | | | |
| Collector–Emitter Sustaining Voltage | $V_{CEO(sus)}$ | $I_C = 100\text{mA}, I_B = 0$ | 100 | – | – | V |
| Collector Cutoff Current | I_{CEO} | $V_{CE} = 50\text{V}, I_E = 0$ | – | – | 1.0 | mA |
| | | $V_{CE} = 100\text{V}, V_{BE(off)} = 1.5\text{V}$ | – | – | 0.5 | mA |
| | I_{CEX} | $V_{CE} = 100\text{V}, V_{BE(off)} = 1.5\text{V}, T_A = +150^\circ\text{C}$ | – | – | 5.0 | mA |
| Emitter Cutoff Current | I_{EBO} | $V_{BE} = 5\text{V}, I_C = 0$ | – | – | 2.0 | mA |
| ON Characteristics (Note 1) | | | | | | |
| DC Current Gain | h_{FE} | $V_{CE} = 3\text{V}, I_C = 10\text{A}$ | 750 | – | 18000 | |
| | | $V_{CE} = 3\text{V}, I_C = 20\text{A}$ | 100 | – | – | |
| Collector–Emitter Saturation Voltage | $V_{CE(sat)}$ | $I_C = 10\text{A}, I_B = 40\text{mA}$ | – | – | 2.0 | V |
| | | $I_C = 20\text{A}, I_B = 200\text{mA}$ | – | – | 3.0 | V |
| Base–Emitter Saturation Voltage | $V_{BE(sat)}$ | $I_C = 20\text{A}, I_B = 200\text{mA}$ | – | – | 4.0 | V |
| Base–Emitter ON Voltage | $V_{BE(on)}$ | $V_{CE} = 3\text{V}, I_C = 10\text{A}$ | – | – | 2.8 | V |
| Dynamic Characteristics | | | | | | |
| Small–Signal Current Gain | h_{fe} | $V_{CE} = 3\text{V}, I_C = 10\text{A}, f = 1\text{kHz}$ | 300 | – | – | |
| Magnitude of Common Emitter Small–Signal Short–Circuit Forward Current Transfer Ratio | $ h_{fe} $ | $V_{CE} = 3\text{V}, I_C = 10\text{A}, f = 1\text{MHz}$ | 4.0 | – | – | MHz |
| Output Capacitance NTE251 NTE252 | C_{ob} | $V_{CB} = 10\text{V}, I_E = 0, f = 0.1\text{MHz}$ | – | – | 400 | pF |
| | | | – | – | 600 | |

Note 1. Pulse Test: Pulse Width = $300\mu\text{s}$, Duty Cycle = 2%



