Vishay General Semiconductor

Schottky Barrier Rectifier



FEATURES

- Guardring for overvoltage protection
- · Very small conduction losses
- Extremely fast switching
- Low forward voltage drop
- High forward surge capability
- High frequency operation
- Solder dip 260 °C, 40 s
- Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC

TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, dc-to-dc converters, and polarity protection applications.

MECHANICAL DATA

Case: DO-201AD

Epoxy meets UL 94V-0 flammability rating

Terminals: Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

E3 suffix for consumer grade, meets JESD 201 class 1A whisker test

Polarity: Color band denotes the cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	1N5820	1N5821	1N5822	UNIT
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	V
Maximum RMS voltage	V _{RMS}	14	21	28	V
Maximum DC blocking voltage	V _{DC}	20	30	40	V
Non-repetitive peak reverse voltage	V _{RSM}	24	36	48	V
Maximum average forward rectified current 0.375" (9.5 mm) lead length at T_L = 95 $^\circ\text{C}$	I _{F(AV)}	3.0			А
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	80			А
Storage temperature range	T _J , T _{STG}	- 65 to + 125			°C

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS	SYMBOL	1N5820	1N5821	1N5822	UNIT
Maximum instantaneous forward voltage (1)	3.0	V _F	0.475	0.500	0.525	V
Maximum instantaneous forward voltage (1)	9.4	V _F	0.850	0.900	0.950	V
Maximum average reverse current at rated DC blocking voltage ⁽¹⁾	T _A = 25 °C T _A = 100 °C	I _R	2.0 20			mA

Note:

(1) Pulse test: 300 μs pulse width, 1 % duty cycle



3.0 A			
V _{RRM} 20 V, 30 V, 40 V			
80 A			
0.475 V, 0.500 V, 0.525 V			
125 °C			
-			





RoHS

COMPLIANT



1N5820 thru 1N5822

Vishay General Semiconductor



THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	1N5820	1N5821	1N5822	UNIT	
Typical thermal resistance ⁽¹⁾	$R_{ extsf{ heta}JA}\ R_{ extsf{ heta}JL}$	40 10			°C/W	

Note:

(1) Thermal resistance from junction to lead vertical P.C.B. mounted, 0.500" (12.7 mm) lead length with 2.5 x 2.5" (63.5 x 63.5 mm) copper pad

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
1N5820-E3/54	1.08	54	1400	13" diameter paper tape and reel		
1N5820-E3/73	1.08	73	1000	Ammo pack packaging		

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current




Figure 3. Typical Instantaneous Forward Characteristics





Figure 4. Typical Reverse Characteristics




1N5820 thru 1N5822

Vishay General Semiconductor



PACKAGE OUTLINE DIMENSIONS in inches (millimeters)





Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.