

Technical Data Sheet

Pow-R-Wash™ Cable Cleaner

PRODUCT DESCRIPTION

The Pow-R-Wash™ Cable Cleaner is a high flash point cleaner that quickly removes soils, adhesives, and residues from insulation jackets and conductors on telecom, fiber optic and coaxial cables. Excellent wetting action lifts and removes soils from the tightest tolerance areas. Pow-R-Wash™ Cable Cleaner is also ideal for removing carbonization, oxidized oils and greases from contacts.


- Removes encrusted dirt, silicone grease and other contaminants
- Leaves no residues
- No odor
- Excellent dielectric strength
- Contains no CFCs or HCFCs
- Contains no chlorinated solvents
- High flash point
- All-Way Spray valve-even sprays upside down

TYPICAL APPLICATIONS

Pow-R-Wash™ Cable Cleaner is engineered to clean:

- Telecom, fiber optic and coaxial cable
- Contacts and Relays
- Equipment and tools

TYPICAL PRODUCT DATA AND PHYSICAL PROPERTIES

Boiling Point	372° F Initial
Flash Point (TCC)	147° F
Evaporation Rate (butyl acetate=1)	<1
Specific Gravity	0.78
Non-Volatile Residue	< 50 ppm
Kauri-Butanol (KB) Number	27
Solubility in Water	Negligible
Dielectric Breakdown (ASTM D-877)	62 kV
VOC* Content:	<u>Aerosol</u>
CARB	50%
SCAQMD	756 g/L
Federal	50%
RoHS Compliant	
Shelflife	5 years

*Volatile Organic Compound (VOC) information is calculated on a weight basis using the VOC definition of California Air Resources Board (CARB) Consumer Product Regulations, South Coast Air Quality Management District (SCAQMD) Rule 102 and the Federal definition published in 40 CFR 51.100(s).

COMPATIBILITY

Pow-R-Wash™ Cable Cleaner is generally compatible with most materials. As with any cleaning agent, solvent/component compatibility must be determined on a non-critical area prior to use.

<u>Material</u>	<u>Compatibility</u>
ABS	Excellent
Buna-N	Excellent
EPDM	Excellent
Graphite	Excellent
HDPE	Excellent
Kynar™	Excellent
LDPE	Excellent
Lexan™	Excellent
Neoprene	Excellent
Noryl®	Excellent
Nylon 66™	Excellent
Cross-Linked PE	Excellent
Polypropylene	Excellent
Polystyrene	Excellent
PVC	Excellent
Silicone Rubber	Excellent
Teflon™	Excellent
Viton™	Excellent

AVAILABILITY

ES2425 13.5 oz. Aerosol

ENVIRONMENTAL IMPACT DATA			
HCFC-141b	None	HFC	None
HCFC-225	None	nPB	None

Hydrochlorofluorocarbons (HCFCs) are regulated under the Montreal Protocol as Class II ozone depleting substances. HCFC-141b is no longer produced in the US under this legislation. HCFC-225 is planned for production phase-out in 2015. Hydrofluorocarbons (HFCs) are not currently regulated.

EPA has listed n-propyl bromide (nPB) as an acceptable alternative to ozone depleting substances in metal, precision, and electronics cleaning under Section 612 of the Clean Air Act.

NOTE:

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. ITW CHEMTRONICS® does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

Chemtronics® is a registered trademark of ITW Chemtronics. All rights reserved. Pow-R-Wash™ and Controlwipes™ are trademarks of ITW Chemtronics. All rights reserved. All other trademarks herein are trademarks or registered trademarks of their respective owners.

MANUFACTURED BY:

ITW CHEMTRONICS
 8125 COBB CENTER DRIVE
 KENNESAW, GA 30152

1-770-424-4888

REV. B (06/09)

<u>DISTRIBUTED BY:</u>

USAGE INSTRUCTIONS

For commercial use only.
 Read MSDS carefully prior to use.
 Spray 4-6 inches from surface to clean.
 Wash parts from top to bottom, allowing the liquid to flush away dirt and dissolved grease. For precise application use attached extension tube. For controlled application, spray into a Controlwipes™ and wipe surface clean.

TECHNICAL & APPLICATION ASSISTANCE

ITW Chemtronics® provides a technical hotline to answer your technical and application related questions. The toll free number is: **1-800-TECH-401.**