102HV & 102V Series - High Voltage Switching Relays SPST - NO, Up to 10mA

The 102V series of reed relays are epoxy encapsulated for HIGH voltage. 102V is capable of 10mA at 5,000VDC. The 102HV is capable of 5mA at 10,000VDC. Typical use includes dielectric testers and medical equipment.



GENERAL SPECIFICATIONS (@ 25° C)

Weight

Contacts:	102HVX	102VX	
Contact Configuration	SPST-NO	SPST-NO	
Contact Material	Tungsten	Tungsten	
Contact Rating			
Maximum Allowable Contact Load	5mA @ 10,000VDC	10mA @ 5,000VDC	
Contact Resistance, Initial	200 milliohms max @ 6VDC	200 milliohms max @ 6VDC	
Coil:			
Coils Available	DC	DC	
Nominal Coil Power	580mW	1.5W	
Input Voltage Tolerance - AC	N/A	N/A	
Input Voltage Tolerance - DC	80% to 110% of nominal		
Drop out voltage	10% of nominal	10% of nominal	
Duty	Continuous	Continuous	
Timing:		00	
Operate Time (max)	3mS	3mS	
Release Time (max)	2mS	2mS	
Dielectric Strength:			
Across Open Contacts	12,000 VRMS	12,000 VRMS	
Between Mutally Insulated Points	12,000 VRMS	12,000 VRMS	
Insulation Resistance	1000 megohms @ 500VAC	1000 megohms @ 500VAC	
	•		
Temperature:			
Operating	-40 to 85°C (-40 to 185°F)	-40 to 85°C (-40 to 185°F)	
Storage	-40 to 105°C (-40 to 221°F)	-40 to 105°C (-40 to 221°F)	
Life Expectancy:			
Electrical (full load operations)	1,000,000	1,000,000	
Mechanical (no load operations)	10,000,000	10,000,000	
, , , , , , , , , , , , , , , , , , , ,			
Miscellaneous:			
Shock	30 G's 11mS, 1/2 Sine Wave	30 G's 11mS, 1/2 Sine Wave	
Vibration	10 G's 10Hz to 1000Hz	10 G's 10Hz to 1000Hz	
Mounting Position	Any	Any	
Enclosure	Potted	Potted	

1.7oz (49 grams)


1.7oz (49 grams)


Special Purpose Relays

Outline Dimensions

Dimensions Shown in inches & (millimeters)

102HV & 102V Wire Diagram (Top View)





Do not hook wire heavier than #22 AWG. Excess stress on terminals could cause damage to internal components.

102HV & 102V Part Number Chart

Part numbers	Contact configuration	Nominal input voltage	Nominal resistance (ohms)	Nominal power (mW)	
5,000 Volts normally open					
102VX-49	SPST-NO	6VDC	70	500	
102VX-50	SPST-NO	12VDC	250	580	
102VX-51	SPST-NO	24VDC	1000	580	
10,000 Volts normally open					
102HVX-3	SPST-NO	24VDC	400	1.5 Watts	