



Vector Part No.: " CG2-65S "


" Nylon Snap-in Card Guides { 5.42" L, 4.50" Ctrs, 6.50" Card Length } for EIA Subracks and VectorPak System "


Part No.	Туре	Length	Centers	Card Length
CG2-45P	Plastic, Screw-in	2.89"	2.25"	4.50"
CG2-45S	Nylon, Snap-in	3.17"	2.25"	4.50"
CG2-50P	Plastic, Screw-in	4.39"	3.75"	5.00"
CG2-65M	Metal, Screw-in	5.42"	4.50"	6.50"
CG2-65P	Plastic, Screw-in	5.42"	4.50"	6.50"
CG2-65S	Nylon, Snap-in	5.42"	4.50"	6.50"
CG2-80P	Plastic, Screw-in	6.64"	6.00"	8.00"
CG2-80S	Nylon, Snap-in	6.93"	7.50"	8.00"
CG2-95M	Metal, Screw-in	8.14"	7.50"	9.50"
CG2-95P	Plastic, Screw-in	8.14"	7.50"	9.50"
CG2-95S	Nylon, Snap-in	8.43"	7.50"	9.50"

Dimensions and Drawing Examples









Description

High quality Snap-in card guides feature tapered slots for easy insertion and removal without tools.

Snap-in card guide can be positioned at 0.25" increments when used with Vector-Pak T-struts (TS169-6/90).

Holes for mounting guides to struts are based on center-to-center multiples of 0.75".

Screw mounted models are available in metal or plastic { installation hardware included }

Screw mounted metal or plastic card guides provide variable positioning along entire length of strut.

Metal or plastic screw down card guides attach with SC4-27/25 flat head screw and NT4-7PA square nut as shown in drawing. All materials are flame retardant.