


VECTORBORD®PLUGBORD™ PART NO. : 4112-5



Description :

4.5" X 4.5" X 0.062, Hole Dia.: 0.042", Grid: 0.100" X 0.100"

Ground Plane / 3-Hole Solder Pad with Zig-Zag Buses

3-hole solder pattern on wiring side

Overall ground plane on component

0.085" diameter clearance around holes

3-hole solder pads (0.28" x 0.080") for interconnecting multiple component leads

Wire-wrap pins to ground planes uses Vector T124 solder washers (T124 available separately)

Layout paper and instructions included..... [Layout Paper\(PDF\)](#)

Circuit Pattern :	Zig-Zag Buses
Contacts :	22/44 @ 0.156" Centers Ni / Gold
16 Pin DIP Capacity :	8
Hole Diameter :	0.042" { 1.0668 mm }
Grid :	0.100" X 0.100" { 2.54mm X 2.54mm }
Dimension { H, W, T } :	4.5" X 4.5" X 0.062"
Material :	CEM-1
Wire-Wrap Terminals :	T44, T46, T49 & T68
Solder Connector :	R644
Wire-Wrap Socket Pins :	R32
Wire-Wrap Connector :	R644-3
Extender :	3690
Recommended Card Cage:	CCK 13 Series Card Cage { Subracks }
NEMA Grade :	FR-4
UL Flammability Class :	94V - 0