Platt Luggage, Inc.

<u>Home</u> > <u>BLOW MOLDED CASES</u> > 507 BLOW MOLDED CASE



Colors Available: BLACK

Product Code: 507

Description

Meet Platt's low cost solution to "Make-Your-Own" case needs. These cases are manufactured from prime, high-density polyethylene, with double wall construction. The textured exteriors resist dents, cracking and scuffs. The shells are unaffected by extreme temperatures. The hardware features mechanical latches that are field replaceable, and a mechanical hinge system that is made to last. All cases meet U.S. 94B Specifications as an electrical insulator and are impervious to chemical attack. All Platt Foam-Filled cases are filled with layers of cubed foam and a flat cushion in the bottom and convoluted and/or flat cushion in the lid.

Case comes with 1 handle, padlock and 2 latches.

Technical Specs

- Exterior Dimensions (L x W x D): 15" x 11" x 4 3/8"
- Interior Dimensions (L x W x D): 13 7/8" x 9 7/8" x 4"
- Shipping Dimensions (L x W x D): 16" x 12" x 5"
- Shipping Weight: 3.00 lbs.

FOAM-FILLED CASES

Blow Molded Cases



Blow Molded Cases

Meet Platt's low cost solution to "Make-Your-Own" case needs.

These cases are foam-filled and manufactured from prime, high-density polyethylene, with double wall construction. The textured exteriors resist dents, cracking and scuffs. The shells are unaffected by extreme temperatures.

The hardware features mechanical latches that are field replaceable and a mechanical hinge system that is made to last.

All cases meet U.S. 94B Specifications as an electrical insulator and are impervious to chemical attack.

to chemical attack.						
Platt#	In	side Di	im.	Out	side D	im.
	L	W	D	L	W	D
102	55/8"	35/8"	$1^{3}/_{8}$ "	61/2"	41/2"	$1^{11}/_{16}$ "
103	55/8"	35/8"	17/8"	$6^{1/2}$ "	41/2"	$2^{1}/_{8}$ "
104	$7^{1}/_{8}$ "	4"	$1^{7}/_{16}$ "	8"	5"	$1^{3}/_{4}$ "
105	$7^{1}/_{8}$ "	4"	$1^{15}/_{16}$ "	8"	5"	$2^{1}/8$ "
106	$7^{1}/_{2}$ "	5"	$1^{11}/_{16}$ "	81/2"	6"	2"
107	$7^{1}/_{2}$ "	5"	$2^{3}/_{16}$ "	81/2"	6"	21/2"
108	$7^{1}/_{2}$ "	5"	211/16"	81/2"	6"	3"
202	81/2"	51/2"	$1^{11}/_{16}$ "	$9^{1}/_{2}$ "	61/2"	2"
203	81/2"	51/2"	211/16"	$9^{1}/_{2}$ "	61/2"	21/2"
204	81/2"	$5^{1}/_{2}$ "	$2^{11}/_{16}$ "	91/2"	61/2"	3"
205	81/2"	$5^{1}/_{2}$ "	$3^{3}/_{16}$ "	91/2"	61/2"	31/2"
206	91/2"	6"	115/16"	101/2"	7"	24/16"
207	$9^{1}/_{2}$ "	6"	211/16"	$10^{1/2}$ "	7"	3"
208	91/2"	6"	37/16"	91/2"	7"	33/4"
302	103/16"	61/2"	115/16"	115/16"	$7^{1/2}$ "	21/4"
303 304	103/16"	61/2"	211/16"	115/16"	71/2"	3"
304	103/16"	61/2"	3 ⁷ / ₁₆ "	115/16"	71/2"	33/4"
306	11" 11"	7" 7"	115/16"	12"	8"	2 ¹ / ₄ " 3"
307	11"	7 7"	$2^{11}/_{16}$ " $3^{7}/_{16}$ "	12" 12"	8" 8"	3 ³ / ₄ "
308	$12^{3}/_{8}$ "	/ 6 ⁷ / ₈ "	3 / 16 2 ⁷ / ₈ "	131/2"	8"	31/4"
309	$12^{3}/_{8}$ "	$6^{7}/_{8}$ "	$4^{1}/_{16}$ "	131/2"	8"	$4^{3}/_{8}$ "
310	$12^{3}/_{8}$ $12^{3}/_{8}$ "	$6^{7}/_{8}$ "	$\frac{4^{1}}{16}$ $\frac{5^{3}}{16}$ "	13 ¹ / ₂ "	8"	5 ¹ / ₂ "
402	12^{7} 8 12^{3} /8"	$7^{7}/8$ "	$\frac{37}{8}$ "	131/2"	9"	31/4"
403	$12^{3}/8$ "	$7^{7/8}$ "	4"	131/2"	9"	$4^{3}/_{8}$ "
404	12 ³ / ₈ "	77/8"	51/8"	131/2"	9"	51/2"
405	123/8"	87/8"	27/8"	131/2"	10"	31/4"
406	$12^{3}/_{8}$ "	87/8"	4"	131/2"	10"	$4^{3}/_{8}$ "
407	123/8"	87/8"	51/8"	131/2"	10"	51/2"
503	$13^{7}/8$ "	87/8"	$2^{7}/8''$	15"	10"	31/4"
504	137/8"	87/8"	4"	15"	10"	$4^{3}/_{8}$ "
505	137/8"	87/8"	51/8"	15"	10"	51/2"
506	$13^{7}/_{8}$ "	$9^{7}/_{8}$ "	$2^{7}/_{8}$ "	15"	11"	31/4"
507	$13^{7}/8$ "	$9^{7}/_{8}$ "	4"	15"	11"	$4^{3}/_{8}$ "
508	$13^{7}/_{8}$ "	$9^{7}/_{8}$ "	51/8"	15"	11"	51/2"
604	$14^{7}/_{8}$ "	$10^{3}/_{8}$ "	$2^{7}/_{8}$ "	16"	111/2"	31/4"
605	$14^{7}/_{8}$ "	$10^{3}/_{8}$ "	4"	16"	111/2"	43/8"
606	$14^{7}/_{8}$ "	$10^{3}/_{8}$ "	51/8"	16"	111/2"	51/2"
607	157/8"	$10^{7}/8$ "	27/8"	17"	12"	31/4"
608 609	15 ⁷ / ₈ "	$10^{7}/8$ "	4" 5 ¹ / ₈ "	17" 17"	12" 12"	$4^{3}/_{8}$ " $5^{1}/_{2}$ "
610	15 ⁷ / ₈ " 16 ⁷ / ₈ "	10 ⁷ / ₈ "		18"	13"	3 /2 4 ¹ / ₄ "
611		11 ¹¹ / ₁₆ " 11 ¹¹ / ₁₆ "		18"	13"	5 ³ / ₈ "
612	$16^{7}/_{8}$ " $16^{7}/_{8}$ "	11/ ₁₆ 11.1/ ₁₆ "	5" 6 ¹ / ₈ "	18"	13"	$6^{1/2}$ "
705	10 ⁷ / ₈ "	1211/16"	0'/8 4 ³ /8"	19"	14"	$4^{3}/_{4}$ "
706	17/8 $17^{7}/8$ "	12^{716} $12^{3}/_{4}$ "	5 ³ / ₄ "	19"	14"	61/4"
707	$17^{7/8}$ $17^{7/8}$ "	12 ³ / ₄ "	71/8"	19"	14"	71/2"
802*	215/16"	145/16"	65/8"	23"	16"	7"
803*	215/16"	145/16"	9 ⁵ / ₈ "	23"	16"	10"
902*	2513/16"	145/16"	65/8"	271/2"	16"	7"
903*	25 ¹³ / ₁₆ "	145/16"	95/8"	271/2"	16"	10"
		/ 10	- 10		-	-

^{*} Molded-in handle reduces "W" dimension usable space.
Please contact Platt Engineering for info

Light-Duty ABS Cases



Light-Duty ABS Cases

This series has been a mainstay of Platt's rugged case line for over 25 years. Light-duty, black, scuff resistant molded ABS thermoplastic forms the tough shell of these cases. Foam-filled, extruded aluminum rim, drawbolt key locks and strong molded handle.

* 1425 has a medium-duty valance

Platt#	Inside Dim.			Body Depth
	L	W	D	
1410	10"	7"	5"	3"
1412	12"	8"	5"	3"
1414	12"	11"	5"	3"
1416	16"	12"	5"	3"
1426	16"	12"	7"	4"
1705	17"	11"	5"	3"
1419	18"	13"	5"	3"
1425*	18"	13"	7"	4"

Medium-Duty ABS Cases



Medium-Duty ABS Cases

Modern look of heavy-duty grained ABS with extruded aluminum frame, these foam-filled cases have a deluxe golf grip handle, cast chrome key locks and piano hinge.

* 2005 has a light-duty valance.

Platt#	Ir	side Din	Body Depth	
	L	W	D	
2005*	20"	14"	5"	3"
2007	20"	14"	7"	4"
2207	22"	16"	7"	4"
2407	24"	18"	7"	4"
2807	28"	20"	7"	4"

Parallel Rib Cases



Heavy-Duty Polyethylene Cases With Stylish Parallel Rib Pattern Without Foam

The exterior shell is tough impact-resistant HMW polyethylene. Heavy-duty aluminum rim with gasket, black trim, molded handle, full-length piano hinge and cast chrome key locks.

ALL PARALLEL RIB CASES FURNISHED WITHOUT FOAM.

Platt#	Inside Dim.			Body Depth
	L	W	D	
141106PR	$14^{1}/_{8}$ "	101/2"	6"	31/2"
171206PR	171/4"	121/2"	6"	31/2"
201675PR	193/4"	153/4"	71/2"	41/2"
221006PR	22"	10"	6"	31/2"
241609PR	233/4"	153/4"	9"	41/2"
251709PR	25"	163/4"	9"	43/4"