



Duplexor

DIMENSIONS (INCHES)





The **Duplexor** is used in control panels where **two loads** are required to alternate to provide equal run time on the loads. The alternating action is initiated by a control switch, which is common with one side of the control voltage. The output contacts will change states each time the control switch is opened, thus alternating the two loads. The LED indicators show the position of the output relay.

The ARA series is the standard Duplexor providing automatic alternating sequence. The ARB has the automatic sequencing feature plus the option of locking it into one sequence. A three position switch permits the field selection of normal duplexing action, locking in the A-B sequence, or B-A sequence.

\\\SPECIFICATIONS				
CONTROL VOLTAGE	24, 120 VAC/DC, 208, 240, 480 VAC, 50/60Hz, 48 VDC, ±10%			
CONTROL SWITCH CURRENT	1 mA			
POWER REQUIRED	3 VA (Approximately)			
DUTY CYCLE	Continuous			
LIFE EXPECTANCY	Mechanical	10,000,000 Operations (Minimum)		
	Electrical	100,000 Operations @ Rated Load		
INDICATORS	LED Shows Output Position			
TEMPERATURES	Operate	-4° to 131°F (-20° to +55°C)		
rating	Storage	-40° to 185°F (-40° to +85°C)		
CONTACT RATING	10 Amps @ 240 VAC, Resistive 1/8 hp @ 120 VAC 1/4 hp @ 240 VAC Inductive 360 VA @ 240 VAC, Inductive			
ENCLOSURE	"A" Lexan® Dust Cover			
TERMINATIONS	Industrial Plug-in			
WEIGHT	4.5 oz.			
NOTE: For Analog signal inputs, ATC offers a duplexing pump				

NOTE: For Analog signal inputs, ATC offers a duplexing pump control — the ATC-Digitec 3800 Panel Meter 480 VAC is not available in the D-DPDT 11-Pin configuration

MODEL NUMBER >>>>> AR			Α	
Type of Alternating Relay				
Standard Duplexor A				
Special Function Duplexor B				
Control Voltage				
24 VAC/DC 24				
48 VDC 48				
120 VAC/DC 120				
208 VAC 208				
240 VAC 240				
380-408 VAC (Consult Factory) 480				
Type of Voltage				
VAC or VAC/DC	Α			
48 VDC only	D			
Contact Configurat	tion			
SI	PDT	В		
DPDT (Cross Wir				
DF	PDT	D		
DPDT (Cross Wired)				
Enclosure Style				