



Style A Only

STYLE A



STYLE N

Single Phase Under Voltage Monitor

The UOA Series offers protection to **single phase** equipment that is required to operate above a certain voltage minimum.

OPERATION

With operating voltage applied above the preset PICK-UP voltage, the internal relay will energize. When the voltage falls below the preset DROP-OUT voltage for a period longer than the release delay, the output relay will de-energize. When line conditions return above the preset PICK-UP voltage, the UOA Series automatically resets and the internal relay energizes.

The HYSTERESIS in each unit provides a differential between the PICK-UP and DROP-OUT trip points.


SPECIFICATIONS

OUTPUT RATING	Style A	DPDT, 5A @ 240 VAC, Resistive; 211 VA @ 240, Inductive.
	Style N	SPDT, 10A @ 240 VAC, Resistive; 180 VA, Inductive.
RESPONSE TIMES	Operate	50 mSEC. (approx.) (500 mSEC. on 12 VDC units)
	Release	0.5 SEC (approx.)
TEMPERATURE RATING	Operate	32° to +131°F (0° to +55°C)
	Storage	-49° to 185°F (-45° to +85°C)
POWER REQUIRED	Models Up To 110 VDC:	3 Watts, Max.
	Models Up To 300 VAC:	5 VA, Max.
WEIGHT	5 oz. to 5.5 oz.	

MODEL NUMBER	DROP-OUT VOLTAGE	PICK-UP VOLTAGE	HYSTERESIS VOLTAGE
<b>UOA-24-A*A</b>	19-27 VAC	21-29 VAC	2
<b>UOA-120-A*A</b>	97-130 VAC	102-135 VAC	5
<b>UOA-208-A*A</b>	177-222 VAC	185-230 VAC	8
<b>UOA-240-A*A</b>	205-250 VAC	215-260 VAC	10
<b>UOA-12-D*A</b>	9-14 VDC	10-15 VDC	1
<b>UOA-24-D*A</b>	19-27 VDC	21-29 VDC	2
<b>UOA-48-D*A</b>	38-53 VDC	40-55 VDC	2
<b>UOA-110-D*A</b>	92-125 VDC	97-130 VDC	5
<b>UOA-220-D*A</b>	185-230 VDC	194-239 VDC	9
<b>UOA-240-D*A</b>	205-250 VDC	215-260 VDC	10
<b>UOA-120-AFN</b>	100 VAC	105 VAC	5
<b>UOA-208-AFN</b>	180 VAC	188 VAC	8
<b>UOA-220-AFN</b>	180 VAC	187 VAC	7
<b>UOA-230-AFN</b>	190 VAC	198 VAC	8
<b>UOA-240-AFN</b>	202 VAC	210 VAC	8


\*ADJUSTMENTS F = Fixed, K = Knob, L = Locknut

WIRING



WIRING DIAGRAMS (SHOWN IN DE-ENERGIZED STATE)

PLUG-IN MODEL Style A



(DC POLARITY SHOWN) RB-08 or PF083A

SURFACE MOUNTED Style N

