



Product Specification: 3585/25 - 3585/50

Date Issued: 4/6/01

Product Description: Round to flat cable, 28 AWG (7/36) tinned copper conductors, polyvinylchloride insulation with a red stripe on the leading edge, aluminum polyester and tinned copper braid shields, with a polyvinylchloride jacket.

Note: All dimensions are in inches unless otherwise specified.

Construction Requirements

Conductor Data:

Material	Tinned Copper
AWG, Stranding	28, 7/36

Insulation Data:

Material	Polyvinylchloride
Nominal Wall Thickness	0.010
Nominal Diameter	0.035
Nominal Overall Width	See Table 1

Core Data:

Number of Conductors	See Table 1
Color Code	Gray With A Red Stripe On The Leading Edge
Termination Length	0.750
Termination Length intervals	1.5

Shield Data:

First Shield	Aluminum/Polyester, Foil Facing Out
Second Shield	Tinned Copper Braid
Nominal Coverage	90%

Jacket Data:

Material	Polyvinylchloride
Color	Black
Nominal Wall Thickness	0.032
Nominal Diameter	See Table 1

Finished Product Requirements:

Temperature	-20°C to 105°C
Voltage Rating	150 - CL2, 300 - AWM
Nominal Capacitance	24 pF/ft
UL AWM Style	20381
UL Type	CL2

Availability:

The standard package is available on 100ft spools, may contain multiple lengths.

Table 1

<u>Part Number</u>	<u># of Conductors</u>	<u>Nominal Width</u>	<u>Nominal Diameter</u>
3585/25	25	1.20	0.34
3585/26	26	1.25	0.35
3585/34	34	1.70	0.36
3585/37	37	1.85	0.38
3585/40	40	1.95	0.40
3585/50	50	2.45	0.46