

NYLON 6/6 - UL9 COLOUR: NATU ITEM No.	-	NATURAL DIM "A'	' ± 0.4
DLCBS2-3-01	L DLCBS2	2-3-19 4.8	}
DLCBS2-4-01	L DLCBS2	2-4-19 6.4	ļ
DLCBS2-5-01	L DLCBS2	2-5-19 7.9)
DLCBS2-6-01	DLCBS2	2-6-19 9.5	;
DLCBS2-7-01	L DLCBS2	2-7-19 11.	1
DLCBS2-8-01	L DLCBS2	2-8-19 12.	7
DLCBS2-9-01	DLCBS2	2-9-19 14.	3
DLCBS2-10-0	1 DLCBS2	-10-19 15.	9
DLCBS2-12-0	1 DLCBS2	-12-19 19.	1
DLCBS2-14-0	1 DLCBS2	-14-19 22.	2




essentracomponents.com


© 2013 Essentra Components. All rights reserved. Registered in England, Company No. 547495. Registered Office: Avebury House, 201-249 Avebury Boulevard, Milton Keynes, MK9 1AU

Condition of Sale can be found on our website: essentra.com.


Essentra Components does not warrant that the files will be error free and may create new versions ("Upgrades") at any time, which may correct such errors. Essentra Components has no obligation to notify you of such upgrades. Any upgraded file will be published to the website, when it becomes available.

You are not permitted to load any of the files on to a network server for the purposes of distribution to one or more other computer(s) on that network or to effect such distribution. Essentra Components shall not be liable for any loss or damage whatsoever or however caused, arising directly or indirectly from the use of the files.





Ø7.1



UNLESS OTHERWISE STATED							
ALL DIMENSIONS IN mm				DO NOT SCALE			
LINEAR TOLERANCE			CE	THIRD ANGLE PROJECTION			
<u>SIZE</u> 0-10mm 10-30mm 30-50mm 50-100mm	(0) ±0.5 ±0.5 ±0.5	±0.30	(0.00) ±0.10 ±0.15 ±0.20 ±0.25	\bigoplus			
100-200mm 200-300mm 300-500mm +500mm	±0.8 ±1.5 ±2.0 ±3.0 ±5.0	±1.20	±0.25 ±0.40 ±0.80 ±1.00 ±1.50	ANGULAR TOLE UNSPECIFIED R DRAFT ANGLE O			
ORG SCALE	2 1						

LINII ECO OTLIEDIMICE CTATED

Z:1

MATERIAL NYLON 6/6

ITEM No.

TITLE

DUAL LOCKING CIRCUIT BOARD SUPPORT - TYPE 2

DWG.No.

DLCBS2

ISSUE No.

1