



APC Back-UPS, 390 Watts / 650 VA, Input 120V /  
Output 120V , Interface Port USB

**Includes:** USB cable, User Manual

**Standard Lead Time:** Usually in Stock



Technical Specifications

Product Overview

Documentation

Software & Firmware

Options

Ratings and Reviews

Output

Output Power Capacity	390 Watts / 650 VA
Nominal Output Voltage	120V
Output Frequency (sync to mains)	60 Hz
Waveform Type	Stepped approximation to a sinewave
Output Connections	(4) NEMA 5-15R (Battery Backup)
	(4) NEMA 5-15R (Surge Protection)



Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Cord Length	1.52 meters
Input voltage range for main operations	90 - 140V
Maximum Input Current	12A



Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Typical recharge time	24 hour(s)
Replacement Battery	<a href="#">RBC17</a>
RBC™ Quantity	1
Runtime Graph	

**Communications & Management**

Interface Port(s)	USB
Control panel	LED status display with On Line : On Battery : Replace Battery and Building Wiring Fault
Audible Alarm	Alarm when on battery : distinctive low battery alarm

**Surge Protection and Filtering**

Surge energy rating	340 Joules
Filtering	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449
Data Line Protection	Network line - 10/100 Base-T Ethernet (RJ-45 connector)

**Physical**

Maximum Height	88.00 mm
Maximum Width	180.00 mm
Maximum Depth	302.00 mm
Net Weight	6.20 KG
Shipping Weight	7.00 KG
Shipping Height	128.00 mm
Shipping Width	235.00 mm
Shipping Depth	393.00 mm
Master Carton Units	2.00
Master Carton Weight	14.40 KG
Color	Black
SCC Codes	1073130428543 1
Units per Pallet	100.00
# of Layers per Pallet	5
# of Units per Layer per Pallet	20

**Environmental**

Operating Environment	0 - 40 °C
Operating Relative Humidity	5 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	5 - 95%
Storage Elevation	0-15000 meters

Audible noise at 1 meter from surface of unit	45.00 dBA
---	-----------

**Conformance**

Regulatory Approvals	CSA C22.2 No. 107.1,FCC Part 15 Class B,FCC Part 68,NOM,TUV-C,UL 1778
Standard Warranty	3 years repair or replace
Environmental Compliance	RoHS,REACH: Contains No SVHCs

\*\*The time to recharge to 90% of full battery capacity following a discharge to shutdown using a load rated for 1/2 the full load rating of the UPS.