


Vishay General Semiconductor


Fast Switching Plastic Rectifier



PRIMARY CHARACTERISTICS						
I _{F(AV)}	1.0 A					
V_{RRM}	50 V to 600 V					
I _{FSM}	30 A					
t _{rr}	200 ns					
I _R	5.0 μΑ					
V _F	1.2 V					
T _J max.	150 °C					

FEATURES





Low leakage current

High forward surge capability

• Solder dip 260 °C, 40 s

 Component in accordance to RoHS 2002/95/EC and WEEE 2002/96/EC

TYPICAL APPLICATIONS

For use in fast switching rectification of power supply, inverters, converters and freewheeling diodes for consumer and telecommunication.

(Note: These devices are not Q101 qualified.)

MECHANICAL DATA

Case: DO-204AL, molded epoxy body Epoxy meets UL 94V-0 flammability rating

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD22-B102

E3 suffix for consumer grade, meets JESD 201 class

1A whisker test

Polarity: Color band denotes cathode end

MAXIMUM RATINGS (T _A = 25 °C unless otherwise noted)								
PARAMETER	SYMBOL	1N4933	1N4934	1N4935	1N4936	1N4937	UNIT	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	٧	
Maximum RMS voltage	V _{RMS}	35	70	145	280	420	٧	
Maximum DC blocking voltage	V_{DC}	50 100 200 400 600				600	٧	
Maximum average forward rectified current 0.375" (9.5 mm) lead length at $\rm T_A = 75~^{\circ}C$	I _{F(AV)}	1.0				Α		
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	30			Α			
Maximum reverse recovery current (1)	I _{RM}	2.0			Α			
Operating junction and storage temperature range	T _J , T _{STG}	- 50 to + 150 °C				°C		

ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)									
PARAMETER	TEST CONDITIONS		SYMBOL	1N4933	1N4934	1N4935	1N4936	1N4937	UNIT
Maximum instantaneous forward voltage	1.0 A		V _F	1.2					٧
Maximum DC reverse current at rated DC blocking voltage		T _A = 25 °C T _A = 100 °C	I _R	5.0 100					μΑ
Maximum reverse recovery time	I _F = 1.0 A, V _R dI/dt = 50 A/μs	= 30 V, s, I _{rr} = 10 % I _{RM}	t _{rr}	200			ns		
Typical junction capacitance	4.0 V, 1 MHz		CJ	12			pF		

Vishay General Semiconductor



THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)							
PARAMETER	SYMBOL	BOL 1N4933 1N4934 1N4935 1N4936 1N4937					UNIT
Typical thermal resistance ⁽¹⁾	$R_{ hetaJA} \ R_{ hetaJL}$	55 25			°C/W		

Note:

(1) Thermal resistance from junction to ambient, and from junction to lead at 0.375" (9.5 mm) lead length, P.C.B. mounted

ORDERING INFORMATION (Example)								
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE				
1N4933-E3/54	0.33	54	5500	13" diameter paper tape and reel				
1N4933-E3/73	0.33	73	3000	Ammo pack packaging				

RATINGS AND CHARACTERISTICS CURVES

(T_A = 25 °C unless otherwise noted)




Figure 1. Forward Current Derating Curves




Figure 3. Maximum Non-repetitive Peak Forward Surge Current




Figure 2. Forward Power Loss Characteristics




Figure 4. Typical Instantaneous Forward Characteristics



Vishay General Semiconductor




Figure 5. Typical Reverse Characteristics




Figure 7. Typical Transient Thermal Impedance





Figure 6. Typical Junction Capacitance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DO-204AL (DO-41)



Note: Lead diameter is $\frac{0.026~(0.66)}{0.023~(0.58)}$ for suffix "E" part numbers



Vishay

Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Document Number: 91000 Revision: 18-Jul-08

www.vishay.com