




Fully Sealed Container Cermet Potentiometer Military and Professional Grade













- Low temperature coefficient (100
- Full sealing
- · Mechanical strength
- Use of faston 2.86 connections
- Tests according to CECC 41 000

DIMENSIONS in millimeters


PE30









DBAN SHAFT LOCKING



PE30 LPRP - WITH LOCATING PEG







Panel sealed version PE30P - PE30PE

PE: Including locating peg





CIRCUIT DIAGRAM



Tolerance unless otherwise specified ± 0.5

Vishay Sfernice

Fully Sealed Container Cermet Potentiometer Military and Professional Grade



SPECIAL FEATURES **COMMAND SHAFT**

Length is measured from the mounting surface to the free end of the shaft. The screwdriver slot is aligned with the wiper within ± 10°. Special shafts are available, in accordance to drawings supplied by customers. We recommend that customers should not machine shafts, in order to avoid damage. Bending or torsion of terminals should also be avoided.

PANEL SEALING: PE30P

The panel sealing device consists of a ring located in a slot on the potentiometer face. Sealing is obtained by tightening the ring against the panel when mounting the potentiometer.

The typical linearity of linear variation law potentiometers is ± 5 %. Guaranteed linearity on request. Consult VISHAY.

SHAFT LOCKING: DBAN

The shaft locking device consists of a tapered nut tightening a slotted notched washer against both bushing and shaft. DBAN tightening torque is 200 Ncm, shaft locking torque

DBAN is also available with all special types.

This device is normally supplied in a separate bag. Can be pre-mounted on request.

LOCATING PEG: LPRP

Location is obtained by fitting a special washer in 2 holes drilled at 180° in the potentiometer face.

ELECTRICAL SPE	CIFICATIONS				
Resistive Element		cermet			
Electrical Travel		270° ± 10°			
Resistance Range	Linear Law	22 Ω to 10 M Ω			
	Logarithmic Laws	100 Ω to 2.2 M Ω			
Standard series E3		1 - 2.2 - 4.7 and on request 1 - 2 - 5			
T-1	Standard	± 20 %			
Tolerance	On Request	± 10 % - ± 5 %			
D D. H	Linear	3 W at + 70 °C			
Power Rating	Logarithmic	1.5 W at + 70 °C			
Temperature Coefficient		See Standard Resistance Element Data			
Limiting Element Voltage (Linear Law)		300 V			
Contact Resistance Variation		3 % Rn or 3 Ω			
End Resistance (Typical)		1 Ω			
Dielectric Strength (RMS)		2500 V			
Insulation Resistance (50	00VDC)	$10^6\mathrm{M}\Omega$			

MECHANICAL SPECIFICATIONS


Mechanical Travel $300^{\circ} \pm 5^{\circ}$ Operating Torque (max. Ncm) 3 typical **End Stop Torque (max. Ncm)** 70 **Max Tightening Torque** of Mounting Nut (Ncm) 250

Unit Weight (max. g) 23 to 32


ENVIRONMENTAL SPECIFICATIONS

Temperature Range - 55 °C to + 125 °C **Climatic Category** 55/125/56 Sealing fully sealed container IP67

POWER RATING CHART



RESISTANCE LAWS



For technical questions, contact: sfer@vishay.com See also: Application notes



Fully Sealed Container Cermet Potentiometer Vishay Sfernice Military and Professional Grade

PERFORMANCE					
	TYPICAL VALUES AND DRIFTS				
TESTS	CONDITIONS	$\frac{\Delta RT}{RT}$ (%) REQUIREMENTS $\frac{\Delta R_{1-2}}{R_{1-2}}$ (%)	$\frac{\Delta RT}{RT}$ (%) $\frac{\Delta R_{1-2}}{R_{1-2}}$ (%)		
Climatic Sequence	Phase A dry heat 125 °C Phase B damp heat Phase C cold - 55 °C Phase D damp heat 5 cycles	± 10 % ± 10 %	± 0.5 % ± 1 %		
Long Term Damp	56 days	± 10 %	± 0.5 % ± 1 %		
Heat	40 °C 93 % HR	Insulation resistance: > 100 $M\Omega$	Insulation resistance: > $10^4 M\Omega$		
Rotational Life	25 000 cycles	± 10 %	± 3 %		
notational Life	23 000 cycles	Contact res. variation: < 7 % Rn	Contact res. variation: < 2 % Rn		
Load Life	1000 h at rated power	± 10 %	± 1 %		
Load Life	90'/30' - ambient temp. 70 °C	Contact res. variation: < 7 % Rn	Contact res. variation: < 3 % Rn		
Rapid Temperature Change	5 cycles - 55 °C at + 125 °C	± 3 %	± 0.5 %		
Shock	50 g at 11 ms 3 successive shocks in 3 directions	± 2 %	± 0.1 % ± 0.2 %		
Vibration 10 - 55 Hz 0.75 mm or 10 g during 6 hours		± 2 %	± 0.1 % ± 0.2 %		

	STANDARD RESISTANCE ELEMENT DATA						A	
STAN-			LINEAR LAW			LOGS LAW		
	DARD RESIS- TANCE VALUES	MAX. POWER AT 70 °C		MAX. CUR. THROUGH WIPER	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. CUR. THROUGH WIPER	TCR -55°C +125°C
	Ω	W	٧	mA	W	V	mA	ppm/°C
	22 47	33	8.12 11.87	369 252				200
	100 220 470 1K 2.2K 4.7K 10K 22K 47K 100K 220K 470K 1M 2.2M 4.7M	3 3 3 3 3 3 1.91 0.90 0.41 0.19 0.09 0.04 0.02 0.01	17.32 25.69 37.55 57.44 81.24 118.74 173.20 256.9 300 300 300 300 300 300 300 300	173 116 79 54 37 25 17 11 6.3 3 1.36 0.63 0.30 0.13 0.06 0.03	1.5 1.5 1.5 1.5 1.5 0.9 0.41 0.19 0.09	38.7 57.4 83.9 122 181.6 265 300 300 300 300	38.7 26.1 17.9 12.2 8.25 5.64 3 1.36 0.63 0.30	±100

MARKING

Printed:

- VISHAY trademark
- model
- NF types if applicable
- ohmic value (in Ω , $k\Omega$ or $M\Omega$)
- tolerance (in %)
- manufacturing date
- marking of terminals 1, 2, 3 or a, b, c

ORDERING INFORMATION								
PE30			AC	200 k Ω	± 20 %	Α	во	e3
MODEL	FEATL	JRE SI	HAFT LENGTH	OHMIC VALUE	TOLERANCE	LAW	PACKAGING	LEAD FINISH
	P Pane sealir	ng* AM	16 mm, slotted 25 mm, slotted 50 mm, plain		± 20 % standard ± 10 % on request	A Linear L clockwise logarithmic inverse F clockwise logarithmic		e3: pure Sn
* PE Panel sealing with locating peg (former designation E108)								

SAP PART NUMBERING GUIDELINES				
P E 3 0 L 0 F G 2 MODEL BUSHING OPTION SHAFT C	OHMIC VALUE TOL LAW PACKAGING SPECIAL			
See the end of this data book for conversion tables (IF APPLICABLE)				

Legal Disclaimer Notice



Vishay

Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

www.vishay.com Revision: 08-Apr-05