CHEMTRONICS[®] Technical Data Sheet

TDS # CW8400

CircuitWorks[®] Lead-Free Flux Dispensing Pens

PRODUCT DESCRIPTION

CircuitWorks[®] Lead-Free Flux Dispensing Pen is designed specifically for lead-free soldering. The convenient pen applies flux where it's needed with precision control. The Lead-Free Flux Dispensing Pen quickly applies a noncorrosive, halide-free, type R flux which meets Bellcore TR-NWT-000078 and passes IPC SF-818 for surface insulation resistance. Instant wetting action provides thorough deoxidation of metallic surfaces providing the best possible surfaces for leadfree soldering.

- Pen dispenser provides controlled and exact application
- Minimizes excess flux on the board
- Completely portable package
- Flux is noncorrosive and halide-free
- Can be used for soldering with lead-free or Tin/Lead solders
- Excellent material compatibility
- Fast drying
- RoHS compliant

TYPICAL APPLICATIONS

CircuitWorks[®] Lead-Free Flux Dispensing Pen precisely dispenses flux on:

- Printed Circuit Boards
- Chip Carriers
- Heat Sinks
- Surface Mount Device Pads
- Switches and Sockets

TYPICAL PRODUCT DATA AND PHYSICAL PROPERTIES

Lead-Free Dispensing Pen – CW8400				
Flux Type	Rosin, Grade WW ROL0			
Flash Point (TCC)	63 °F (17 °C)			
Vapor Density (air=1)	> 1			
Appearance Liquid	ClearYellow			
Odor	Alcohol			
Shelflife	2 years			
RoHS/WEEE Status	RoHS WEEE Compliant			

COMPATIBILITY

CircuitWorks[®] Lead-Free Flux Dispensing Pen is generally compatible with most materials used in the electronics industry. As with any cleaning agent, material compatibility should be determined on a noncritical area prior to use.

USAGE INSTRUCTIONS

For industrial use only. Read MSDS carefully prior to use.

Hold pen vertically and briefly depress tip to start liquid flow. Rub pen tip on surface to be fluxed. After soldering, wipe area around soldered joint using a ControlWipeTM dry wipe to remove unreacted flux.

Flux residues are designed to be left on the board, however, they can be easily cleaned with Chemtronics Flux-Off[®] Lead-Free Flux Remover (ES897B or ES1697) or CircuitWorks[®] Lead-Free Flux Remover Pen (CW9400).

CAUTION: Product is Flammable - Do not use near sources of ignition and energized equipment.

AVAILABILITY

CW8400

9 gm (0.32 oz)

NOTE: This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly.

ITW CHEMTRONICS[®] does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

Chemtronics[®] and CircuitWorks[®] are registered trademarks of ITW Chemtronics. All rights reserved. ControlWipe[™] is a trademark of ITW Chemtronics. All rights reserved.

SECTION 1: CHEMICAL PRODUCT AND COMPANY INFORMATION

MSDS #3118

Product Information: 800-TECH-401

Product Identification

CIRCUITWORKS [®] LEAD-FREE FLUX DISPENSING PEN						
Product Code: CW8400						
SECTION 2: COMPOSITION/INFORMATION ON INGREDIENTS						
Product Ingredient Information	CAS#	Wt. % Range				
Isopropanol	67-63-0	70-90				
Rosin	8050-09-7	10-20				
Tripropylene glycol butyl ether	55934-93-5	1-5.0				
Mineral Spirits	64742-88-7	1-5.0				

SECTION 3: HAZARD IDENTIFICATION

Emergency Overview: Clear, yellow liquid with strong alcohol odor. This product is flammable. Liquid will irritate eyes and skin under repeated or prolonged exposure. Breathing high concentrations of product vapor may produce drowsiness and a headache.

 Potential Health Effects:

 Eyes:
 Liquid and vapors of this product are irritating and can cause pain, tearing, reddening and swelling accompanied by a stinging sensation. Vapors released

from the soldering process may cause eye irritation.

<u>Skin:</u> Prolonged contact may cause skin irritation and/or sensitization.

Ingestion: Harmful if swallowed. Irritating to mouth, throat and stomach. May cause vomiting.

Inhalation: Harmful if inhaled. High concentrations of vapors in immediate area can displace oxygen and can cause dizziness and unconsciousness, with longer exposure. Vapors from soldering processes may cause irritation of the nose and throat. Respiratory sensitization may result from inhalation of rosin fumes. Pre-Existing Medical Conditions Aggravated by Exposure: Heart, lung, skin, eye.

SECTION 4: FIRST AID MEASURES

Eyes: If eye irritation occurs immediately flush with plenty of water. After initial flushing, remove any contact lenses and continue flushing for at least 15 minutes. Have eyes examined and tested by medical personnel if irritation develops or persists.

Skin: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persist. Wash clothing separately before reuse. Ingestion: Swallowing less than an ounce will not cause significant harm. For larger amounts, do not induce vomiting, but get immediate medical attention.

Inhalation: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen and get immediate medical attention.

SECTION 5: FIRE FIGHTING MEASURES

Flash Point: 62°F (17C) (TCC)

LEL/UEL: Not established (% by volume in air)

Extinguishing Media: Use alcohol foam, carbon dioxide, or water spray when fighting fires involving this material.

Fire Fighting Instructions: As in any fire, wear self-contained breathing apparatus (pressure-demand, OSHA/NIOSH approved or equivalent) and full protective gear.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Spills: Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container for proper disposal. Do not flush to sewer. Avoid runoff into storm sewers and ditches which lead to waterways.

SECTION 7: HANDLING AND STORAGE

Avoid prolonged or repeated contact with eyes, skin, and clothing. Wash hands before eating. Use with adequate ventilation. Avoid breathing product vapor or mist. Do not reuse this container. Store in a cool dry place away from heat, sparks and flame. Keep container closed when not in use. Do not store in direct sunlight. **KEEP OUT OF REACH OF CHILDREN.**

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION Exposure Guidelines: CHEMICAL NAME ACGIH TLV ACGIH STEL OSHA PEL Isopropanol 200 ppm 400 ppm 400 ppm Tripropylene glycol butyl ether NA NA NA Mineral Spirits 200 ppm NA NA Work/Hygienic Practices: Ventilation is recommended to control airborne levels of soldering process vapors. Wear safety glasses with side shields (or goggles) and chemical resistant gloves when handling this material. NFPA and HMIS Codes: NFPA HMIS Health 1 1 3 Flammability 3 0 0 Reactivity Personal Protection - B SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES Physical State: Yellow liquid Solubility in Water: Soluble Odor: Alcohol Specific Gravity: (Water =1) 0.81 pH: NA Evaporation Rate: > 1 Vapor Pressure: 33 mm Hg @ 68°F (Butyl acetate =1) Vapor Density: 2.0 Viscosity: 1 (Approx.) (Air =1) (Water = 1) Boiling Point: 180°F (82C) Percent Volatile: < 95 %

SECTION 10: STABILITY AND REACTIVITY

<u>Stability -</u> This product is stable.

Conditions to Avoid: Do not use near open flames, red hot surfaces or other sources of ignition.

Incompatibility: Do not mix with strong acids or strong oxidizing agents.

Products of Decomposition: Thermal decomposition may release carbon monoxide, carbon dioxide and incompletely burned hydrocarbons.

Hazardous Polymerization: Will not occur.

SECTION 11: TOXICOLOGICAL INFORMATION								
Toxicological Information								
Inhalation:			Ingestion:					
Isopropanol	LC50/rats	12,000 ppm/8hr	Isopropanol	LD50 rats	5,045 mg/kg			
<u>Skin:</u>			Eye:					
Isopropanol	Rabbit LD50	12,800 mg/kg	Isopropanol	rabbit N	/ILD-MOD			
Cancer Information: No ingredients listed as human carcinogens by NTP or IARC								
Reproductive effects: none	Teratoge	Mutagenic effects: none						

SECTION 12: ECOLOGICAL INFORMATION

Environmental Impact Information

Avoid runoff into storm sewers and ditches which lead to waterways. Water runoff can cause environmental damage.

REPORTING

US regulations require reporting spills of this material that could reach any surface waters. The toll free number for the US Coast Guard National Response Center is: 1-800-424-8802

SECTION 13: DISPOSAL CONSIDERATIONS Dispose of in accordance with all federal, state and local regulations. Water runoff can cause environmental damage. SECTION 14: TRANSPORTATION INFORMATION								
	Proper Shipping Name	UN Number	<u>Class</u>	Sub. <u>Risk</u>	Pkg. <u>Group</u>	Hazard <u>Label</u>	Pkg. <u>Instr./Auth</u>	Max. <u>Quantity</u>
<u>Air:</u>	Flammable liquid n.o.s. (Isopropanol)	UN 1993	3	NA	Π	Flammable liquid	305	1L
Ground:	Consumer Commodity ORM-D	NA	NA		NA	ORM-D	173.150	

SECTION 15: REGULATORY INFORMATION

SECTION 313 SUPPLIER NOTIFICATION

This product contains no toxic chemicals subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372).

This information should be included on all MSDSs copied and distributed for this material.

TOXIC SUBSTANCES CONTROL ACT (TSCA).

All ingredients of this product are listed on the TSCA Inventory.

WHMIS: Class B2; Class D2B

This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR.

SECTION 16: OTHER INFORMATION

Product should be used only with adequate ventilation. Mechanical ventilation is recommended on all soldering stations. If such ventilation is not available, personnel should wear NIOSH approved organic vapor respirators equipped with particulate dust filters specified for use during welding or soldering.

To the best of our knowledge, the information contained herein is accurate. However, all materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist.