## CHEMTRONICS<sup>®</sup> Technical Data Sheet

## **TDS # CW2400**

# **CircuitWorks<sup>®</sup> Conductive Epoxy**

### **PRODUCT DESCRIPTION**

CircuitWorks<sup>®</sup> Conductive Epoxy is a two part, silver epoxy used in prototype, repair general conductive bonding and applications. CW2400 features strong mechanical bonds, excellent electrical conductivity, and quick room temperature curing. CircuitWorks<sup>®</sup> Conductive Epoxy bonds aggressively to a wide variety of materials.

- Two-component product
- Simple mixing ratios
- Excellent electrical conductivity
- Fast curing
- High strength bond
- Bonds dissimilar surfaces
- Operating temperature range from
- -91°C (-131°F) to 100°C (212°F)

### **TYPICAL APPLICATIONS**

CircuitWorks<sup>®</sup> Conductive Epoxy may be used for electronics applications including:

- Conductive Bonds Between Heat Sensitive Components
- Solderless Surface Mount Connections
- Circuit Board Trace Repair
- Static Discharge and Grounding
- Solder Repair
- Conductive Structural Adhesions

### TYPICAL PRODUCT DATA AND PHYSICAL PROPERTIES

#### Composition

composition		
Material	Part A Part B	Epoxy Hardener
Specific Gravity (Parts A & B Mix	ed)	2.85
Cured Compou	ınd	
Volume Resistivit	У	<0.001 ohm-cm
Thermal Conductiv	ity	
Cal-cm/sec-cm <sup>2</sup> - $^{\circ}$ C		$3.8 \times 10^{-3}$
BTU-in/hr-ft <sup>2</sup> -°F		11.0
W/m°K		1.6
Operating Temper	ature	-131 to 212°F
Range		(-91 to 100°C)
Lap Shear (ASTM D-1002)		>1200 lbs/in <sup>-</sup>
Shore Hardness		>70
Adhesion		Excellent
Cured Flexibility		Excellent
Chemical Resistar	nce	Excellent
Moisture Resistan	ce	Good
Typical Thickness	5	5 mil
Shelflife		12 months
Conditions: Store	at temperati	ures below 120° F

### COMPATIBILITY

CircuitWorks<sup>®</sup> Conductive Epoxy is generally compatible with most materials used in printed circuit board fabrication. As with any adhesive/sealant, compatibility with substrate should be determined on a non-critical area prior to use.

#### **USAGE INSTRUCTIONS Read MSDS carefully prior to use.**

**Cleaning:** For best results, clean the board with one of Chemtronics<sup>®</sup> Electro-Wash<sup>®</sup> or Pow-R-Wash<sup>®</sup> cleaners in order to remove any surface contamination which may prevent adequate material contact.

**Mixing:** Mix equal amounts (1:1) by weight or volume of Part A and Part B. Mix thoroughly for 2 minutes and apply within 8 minutes.

**Thinning:** Do not attempt to thin.

**Curing:** Curing times and electrical depend conductivity primarily on For fastest curing times, temperature. maximum conductivity and adhesion, cure the bond between 150-250°F (65-121°C) for 5-10 minutes. CircuitWorks<sup>®</sup> Conductive Epoxy can be room temperature cured at or above 75°F (25°C), for 4 hours. Maximum conductivity and bond strength are achieved in 24 hours. Curing at temperatures below 75°F (25°C) will result in a loss of conductivity and adhesion.

**Pot Life:** 8-10 Minutes at 75°F (25°C) after mixing.

### AVAILABILITY

CW2400

7g/ 0.25 oz. Adhesive & 7g/ 0.25 oz. Hardener

### NOTE:

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. CHEMTRONICS<sup>®</sup> does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

#### SECTION 1: CHEMICAL PRODUCT AND COMPANY INFORMATION

MSDS #4002B

Product Information: 800-TECH-401

CI	RCUITWORKS® CONDUCTIVE EPOXY - P	art B (Hardener)	
Product Code: CW2400, CW2400J, CW2400BL	K (Part B)		
SECTION 2: COMPOSITION/INFORMATION	ON INGREDIENTS		
Chemical Name	CAS No.		Wt. % Range
Silver (Metallic)	7440-22-4		60.0-90.0
Modified Aliphatic Amine	140-31-8		10.0-25.0
SECTION 3: HAZARDOUS IDENTIFICATION	I		
Emergency Overview: Silver/gray paste with amine		y cause chemical burns in eve	
Potential Health Effects:	odor. This product is nonmanimable. Elquid ma	y cause chemical burns in eye.	
Eyes: This product may cause chemical burns in the	eve Damage is irreversible		
Skin: Sensitizer - may cause allergic skin reaction.	e eye. Damage is inteversible.		
ngestion: Harmful if swallowed. May cause che	mical irritation in gastrointestinal tract and max	be potentially toxic. Silver	ingestion may result in generalize
rgyria.		se potentially tonici. Shiver	ingestion may result in generality
<u>nhalation:</u> May cause respiratory irritation if inhale	d over a long period of time. Sensitizer - may cat	use allergic respiratory reaction	1.
Pre-Existing Medical Conditions Aggravated by Exp		8 I J	
SECTION 4: FIRST AID MEASURES			
Eyes: Immediately flush with large amounts of wa	ater After initial flushing remove any contact	lenses and continue flushing	for at least 15 minutes Have ev
examined by a Physician.	act. Ther initial husining, remove any contact	ienses and continue mushing	for at least 15 minutes. Trave eye
<u>Skin:</u> Remove contaminated clothing and wash skin	with soap and water. Get medical attention if irr	itation persists. Wash clothes	separately before reuse
ngestion: If swallowed, seek medical attention. No			
nhalation: In case of exposure to high concentration		hing is difficult, give oxygen a	nd call a Physician. If breathing h
topped, apply artificial respiration and call a Physic		8	,
ECTION 5: FIRE FIGHTING MEASURES			
Flash Point: $> 200^{\circ}F$ (>93C) (Setaflash)	LEL/UEL: NA (% by volume in air)		
Extinguishing Media: Use carbon dioxide or dry che		large fires	
Fire Fighting Instructions: Remove all ignition so			sed to extreme heat As in any fir
vear self-contained breathing apparatus (pressure de			sed to extreme neat. Ats in any m
SECTION 6: ACCIDENTAL RELEASE MEAS			
<u>Large Spills:</u> Remove all sources of ignition (spa		asthing apparatus and approp	riata parsonal protactiva aquinmar
Ventilate area and contain and absorb spill with ine			
proper disposal. Do not flush to sewer. Prevent mat			ice in a chemical waste container f
Small Spills: Absorb spill with absorbent material, t			
	nen place in a chemical waste container for prope	a disposai.	
SECTION 7: HANDLING AND STORAGE			
Avoid prolonged or repeated contact with skin, eye	s or clothing. Wash hands before eating. Use w	with adequate ventilation. Avo	bid breatning product vapor. Do no
euse this container. Store in a cool dry place, away	from neat, sparks or flames.		
<b>KEEP OUT OF REACH OF CHILDREN.</b>			
SECTION 8: EXPOSURE CONTROLS, PERSO	NAL PROTECTION		
Exposure Guidelines:			
CHEMICAL NAME	ACGIH TLV	OSHA PEL	ACGIH STEL
Silver	0.1 mg/m3	0.01mg/m3	NA
Modified Aliphatic Amine	NA	NA	NA
Vork/Hygienic Practices: Good general ventilation	n should be sufficient to control sinhows level	a Logal approvat vantilation a	any ha management to control any a
ontaminants to within their TLVs during the use of			
andling this material.	this product. Wear safety glasses with side sher	is of goggles and tubber of ou	ter chemically resistant gloves whe
VFPA and HMIS Codes:	NFPA	HMIS	
Health	1	1	
Flammability	1	1	
Reactivity	0	1 0	
Personal Protection	-	B	
	OPEDITIES	U.	
SECTION 9: PHYSICAL AND CHEMICAL PR			
Physical State: Silver/gray Paste		Solubility in Water: <10%	

Physical State:Silver/gray PasteSolubility in Water: <10%</th>Odor:AmineSpecific Gravity:2.5-2.8pH: NAEvaporation Rate: <1</td>Vapor Pressure:<1.0 mmHg @ 20°C</td>(Butyl acetate=1)Percent Volatile:<0.5%</td>Boiling Range: >400°F (>204C)Vapor Density:>1(Air = 1)

60.0-90.0%

#### SECTION 10: STABILITY AND REACTIVITY

Stability: This product is stable. Conditions to Avoid: Excessive Heat.

Incompatibility: Avoid epoxy resins and isocyanates, strong acids, mineral and organic acids, strong bases, caustics and alkali contamination.

Products of Decomposition: Carbon monoxide, carbon dioxide and oxides of nitrogen.

Hazardous Polymerization: Will not occur.

Conditions to avoid: Contamination with strong acids, bases, epoxy resins or isocyanates can cause polymerization.

	LD50	LD50	LC50 (ppm)	
Ingredients	(rat) Oral	(rbt) Dermal	(rat) Inhalation	
Silver (metallic)	NA	NA	NA	
Modified Aliphatic Amine	2,140 mg/kg	880 µL/kg	NA	
Cancer Information: No ingredient	s listed as human carcinogens by NTF	or IARC		
Reproductive effects: none	Teratogen	ic effects: none	Mutagenic effects: none	

#### SECTION 12: ECOLOGICAL INFORMATION

**Environmental Impact Information** 

Avoid runoff into storm sewers and ditches which lead to waterways. Water runoff can cause environmental damage.

#### REPORTING

US regulations require reporting spills of this material that could reach any surface waters. The toll free number for the US Coast Guard National Response Center is: 1-800-424-8802

### SECTION 13: DISPOSAL CONSIDERATIONS

Dispose of in accordance with all federal, state and local regulations. Water runoff can cause environmental damage.

#### SECTION 14: TRANSPORTATION INFORMATION

Air and Ground Shipments:

Adhesives, sealants Not Regulated

#### SECTION 15: REGULATORY INFORMATION

SECTION 313 SUPPLIER NOTIFICATION

This product contains the following toxic chemicals subject to the reporting requirements of Section 313 of the Emergency Planning and Community Right-To- Know Act of 1986 (40 CFR 372).

Silver CAS # 7440-22-4 This information should be included on all MSDSs copied and distributed for this material.

TOXIC SUBSTANCES CONTROL ACT (TSCA).

All ingredients of this product are listed on the TSCA Inventory.

WHMIS: Class D2B

This product has been classified according to the hazard criteria of the CPR and the MSDS contains all of the information required by the CPR.

#### SECTION 16: OTHER INFORMATION

Normal ventilation for standard manufacturing practices is usually adequate. Local exhaust should be used when large amounts are released.

To the best of our knowledge, the information contained herein is accurate. However, all materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist.