

Splice Cap Crimp Connectors

- Designed for making fast, permanent, pressure-type connections
- Solid copper sleeves require less crimping pressure
- Resist corrosion in harsh environments
- Tin-plated steel sleeves also available (pg. A-19)
- UL 486C Listed and CSA C22.2 #188 Certified; comply with Federal Specification W-S-61D

Description	Wire Combination Range (Inches)	Quantity	Cat. No.
Copper Crimp Connector	600V* 18 to 10 AWG Min. 2 #18 Max. 4 #12	Box of 100	2006S
		Bag of 1,000	2006SB
Copper Crimp Connector	600V* 14 to 4 AWG Min. 2 #10 Max. 2 #6	Box of 50	2011S
		Bag of 500	2011SB

*1,000V maximum in fixtures and signs



Splice Cap Insulators

- Convenient, safe and fast installation
- Snap-on nylon construction
 Rated at 105°C (221°F) –
- 600V (1,000V maximum in fixtures and signs)

For Connector Model	Quantity	Cat. No.
2006S	Box of 100	2007
20005	Bag of 1,000	2007B
2011S	Box of 50	2014
20115	Bag of 500	2014B

Four-Way Crimp Tool

- Patented design ensures even compression and reliable connectors
- Spring-loaded, cam-actuated plungers
- Fingertip adjustment for different connector sizes

Description	Cat. No.
Four-Way Crimp Tool	C-24