

Interface Plug-in Relay XT

- 1 pole 16 A, 2 pole 8 A, 1 CO contact or 2 CO contacts
- DC- or AC coil, sensitive coil 400 mW
- Reinforced insulation, protection class II (VDE 0700)
- 4 kV / 8 mm coil-contact
- Manual test tab, optionally lockable¹⁾
- Version with mechanical and/or electrical indicator optionally available
- Suitable for use in Tyco standard RT sockets
- Recycleable packaging

Applications

Panel boards, mechanical engineering

Approvals
REGNr. B758, c us E214025
Technical data of approved types on request

Contact data	1-pole	2-pole	
Contact configuration	1 CO	2 CO	
Contact set	single	contact	
Type of interruption	micro disconnection		
Rated voltage / max. switching voltage AC	240 / 4	100 VAC	
Rated current	16 A	8 A	
Limiting continuous current	16 A	8 A, UL: 10 A	
Maximum breaking capacity AC	4000 VA	2000 VA	
Limiting making capacity,max 4 s, df 10%	30 A	15 A	
Contact material	AgNi 90/10		
Rated frequency of operation with / without load	6 / 600 min ⁻¹		
Operate- / release time DC coil	max 8 / 6 ms	max 10/5 ms	
Bounce time DC coil, NO / NC contact	max 4 / 6 ms	max 4/9 ms	

Contact ratings

Cycles
30x10 ³
50x10 ³
50x10 ³
100x10 ³
30x10 ³
20x10 ³
30x10 ³
-

Coil data		
Rated coil voltage range DC coil	6110 VDC	
AC coil	24230 VAC	
Operative range to IEC 61810	2	
Coil insulation system according UL1446	class F	
Coil insulation system according UL1446	class F	


¹⁾ Locking function description


If the test button is pulled out too forcefully, it may bypass the momentary testing position and go straight into the locked position.


Delivery status is with testing possibility only, to reach locking position please remove the locking plastic pip according drawing.



F0289-B







Datasheet Rev. HK1 Issued 2008/11 www.tycoelectronics.com www.schrackrelays.com

Dimensions are in mm unless otherwise specified and are shown for reference purposes only.

Product specification according to IEC 61810-1. Product data, technical parameters, test conditions and

processing information only to be used together with the 'Definitions' section in the catalogue or at schrackrelays.com in the 'Schrack' section.

Specifications subject to change.





Interface Plug-in Relay XT (Continued)

Coil	versions,	DC-coil
------	-----------	---------

LED &	Rated	Operate	Release	Coil	Rated coil	opt. LED
PD*	voltage	voltage	voltage	resistance	power	power
	VDC	VDC	VDČ	Ohm	mW	mW
LB2	12	8.4	1.2	360±10%	400	10
LC4	24	16.8	2.4	1440±10%	400	19
LE8	48	33.6	4.8	5520±10%	417	39
MB0	110	77.0	11.0	28800±12%	420	87
	PD* LB2 LC4 LE8	PD* voltage VDC LB2 12 LC4 24 LE8 48	PD* voltage VDC voltage VDC LB2 12 8.4 LC4 24 16.8 LE8 48 33.6	PD* voltage VDC voltage VDC voltage VDC LB2 12 8.4 1.2 LC4 24 16.8 2.4 LE8 48 33.6 4.8	PD* voltage VDC voltage VDC voltage VDC voltage VDC resistance Ohm LB2 12 8.4 1.2 360±10% LC4 24 16.8 2.4 1440±10% LE8 48 33.6 4.8 5520±10%	PD* voltage voltage voltage voltage resistance power VDC VDC VDC Ohm mW LB2 12 8.4 1.2 360±10% 400 LC4 24 16.8 2.4 1440±10% 400 LE8 48 33.6 4.8 5520±10% 417

All figures are given for coil without preenergization, at ambient temperature +23°C *) Protection diode PD; standard polarity: +A1 /-A2

Other coil voltages on request

Coil versions, AC-coil Coil LED Rated Operate Release Coil Rated coil opt. LED voltage voltage voltage code resistance power power 50/60 Hz 50/60 Hz 50/60 Hz 50/60 Hz VAC VAC VAC Ohm VA VA 524 **R24** 24 **18.0** / 19.2 3.6 350±10% **0.76** / 0.58 0.012 615 S15 115 86.3 / 92.0 17.3 8100±15% 0.76 / 0.58 0.054 **172.5** / 184.0 32500±15% 0.073 730 T30 230 34.5 0.74 / 0.58

All figures are given for coil without preenergization, at ambient temperature +23°C Other coil voltages on request

Insulation

Dielectric strength coil-contact circuit	5000 V _{rms} in combination with RT78726
	4000 V _{rms} in combination with RT78725
open contact circuit	1000 V _{rms}
adjacent contact circuits	2500 V _{rms}
Clearance / creepage coil-contact circuit	≥ 8 / 8 mm
Material group of insulation parts	Illa
Tracking index of relay base	PTI 175 V
Insulation to IEC 60664.1	

Adjacent contact circuits 2500 Vrms

Clearance / creepage coil-contact circuit ≥ 8 / 8 mm

Material group of insulation parts IIIa

Tracking index of relay base PTI 175 V

Insulation to IEC 60664-1

Type of insulation coil-contact circuit open contact circuit adjacent contact circuits

Rated insulation voltage 250 V

Pollution degree 3 2

Rated voltage system 240 V 230 / 400 V


Overvoltage category III


Other data	1-pole	2-pole
Mechanical endurance DC coil	> 10 >	(10 ⁶
AC coil	> 5 x	10 ⁶
Material		
RoHS - Directive 2002/95/EC	comp	liant
Environment	·	
Ambient temperature range DC coil	-40+	70°C
AC coil	-40+	70°C
Vibration resistance (function), NO / NO	C cont. 20 / 5 g, 30	500 Hz
Shock resistance (destruction)	100	g
Category of protection	RT	IĪ
Processing		
Mounting distance	≥ 4,5 mm, dense p	acking of sockets
Relay weight	16	g
Packaging unit	10 / 25	Ō pcs

Accessories

For Details see datasheet Accessories Interface Power Relay XT


TE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1, table 12); for relays mounted on sockets deratings may apply.







Terminal assignment

Bottom view on pins












Interface Plug-in Relay XT (Continued)



Product key	Contacts	Cont. material	Coil	Coil	Part number
XT374LC4	1 CO contact	AgNi 90/10	DC-coil	24 VDC	1887112-1
XT374R24	16 A	test button,	AC-coil	24 VAC	1887113-3
XT374T30		mechanical		230 VAC	1887113-1
XT484LC4	2 CO contacts	and electrical	DC-coil	24 VDC	1887212-1
XT484R24	8 A	indicator	AC-coil	24 VAC	1887213-3
XT484T30				230 VAC	1887213-1

change.