Automatic Timing & Controls

DIGITAL SETTING: The 425A is set digitally by rotating each setting knob until the desired Time Preset is displayed by the number wheels on the front of the timer. The digital setting allows exact, accurate and repeatable timing cycles.

HIGH ACCURACY: The 425A utilizes a crystal controlled oscillator which provides 0.1% timing accuracy across all rated voltages and temperatures.

CYCLE PROGRESS INDICATION: The 425A offers the industry's brightest green LED display in a 1/16 DIN package. Depending on the Model, the three-digit LED display will time UP to or DOWN from the Time Preset.

Through its internal microcontroller, the 425A keeps track of the time setting by monitoring each of the three Time Preset switches. Whenever a change is made in the time preset, even during a cycle, the 425A instantly re-computes and adjusts the current timing cycle.

1/16 DIN HOUSING: The 48mm² (1/16 DIN) housing is compact, allowing the 425A to be panel mounted or plug-in using an 8-pin octal socket. The decimal point and SEC/MIN/HRS switches are located on the side of the unit. When panel mounted, these range switches are not accessible to the operator. This Tamper-proof feature prevents unauthorized or hazardous changes to the timing range.

MEMORY OPTION: The 425A can be ordered as standard with an EEPROM memory. This allows the 425A to retain the elapse time or time remaining during momentary or sustained power interruptions.

INSTANTANEOUS AND DELAYED RELAY VERSIONS: A version of the 425A is available with one set of SPDT instantaneous contacts and one set of SPDT delayed contacts.

DELAYED RELAY VERSION: A version of the 425A is available with DPDT delayed contacts.

MODEL 425A300Q10XX (SPDT INSTANTANEOUS & SPDT

DELAYED RELAYS): Timing starts when power is applied to terminals 2 and 7. The instantaneous relay energizes, the LED digital display begins to increment from 0 and the timing LED blinks slowly. When the preset value is reached, the LED blinks rapidly and the Delayed SPDT relay is energized. The timer remains in this timed-out condition until reset by removing power.

MODEL 425A300Q20XX (DPDT DELAYED RELAY): Timing starts when power is applied to terminals 2 and 7. The LED display begins to increment from 0 and the timing LED blinks slowly. When the preset value is reached, the LED stops, the timing LED blinks rapidly and the Delayed DPDT relay energizes. The timer remains in this timed-out condition until reset by removing power.

MODEL 425A300Q10MX & MODEL 425A300Q20MX

(MEMORY OPTION): Operation is same as above, however, units will not reset when power is removed during the timing cycle. Timers with this option can only be reset after time-out, or by adjusting the setting knobs to 000 during the timing cycle.

CAUTION: Be advised that the relay(s) will transfer when setting knobs are adjusted to 000 when power is applied.


- Easy-To-Read High Intensity Green LED Display
- Timing From .01 SEC to 999 Hrs in One Unit
- Switch Selectable Timing Ranges Are Tamper Proof When Panel Mounted
- Timing LED Indicates Output Relay Status
- Time Preset Can Be Adjusted While Timing
- e al banel rroof Digital Display Timer Permory Option
 - Passes NEMA Showering Arc Noise Test
 - Panel Mounting or 8-pin Octal Plug-in mounting
 - Timing Up to or Down From the Set Point

	1						
MODEL NUMBER >>>>>	425A	300					
	Range						
0 to 9.99 or 99.9 or 999 SEC, MIN, HR 300							
Voltage & Frequency							
120 VAC - 240 VAC 50/60 Hz G							
120 VAC 50/60 Hz Q							
Output Arrangement							
Instantaneous Relay (SPDT), Delay Relay (SPDT)							
Delay Relay (DPDT)							
Memory							
Standard-No Memory X							
With Memory (EEPROM) M							
Features							
Standard (Time Up)						Х	
Standard (Time Down)						D	
Special						К	
Accessories							
8-Pin surface/DIN rail socket 0000-825-85-00							
Hold down clips for above socket 0407-025-13-00							
Panel mounting bracket 0405-320-02-00							
Plug-in socket kit (8-pin) 0319-261-45-00							

8-Pin socket w/rear facing terminals 600-3-0011

425A Series

SPECIFICATIONS



JILCI	ICATIONS			
	425A300Q10XX	ON-Delay Time Up		
MODELS	425A300Q20XX	ON-Delay Time Up		
	425A300Q10XD	ON-Delay Time Down		
	425A300Q20XD	ON-Delay Time Down		
RANGES	Switch Selectable, 0 to 9.99, 99.9 or 999 Sec/Min/Hrs			
	Туре	Q10 Models: SPDT, Q20 Models: DPDT		
load relay	Life	10 Million operations (no load)		
	Contact Rating	5 AMPS Resistive @ 250 VAC 30 VDC, or 1/10HP @ 120 VAC		
TEMPERATURE RATING	0° to 140°F (-18° to 60°C)			
noise Immunity	Showering ARC per NEMA ICS2-230, the 425A will withstand a voltage surge of 4500 volts for 50 microseconds without damage			
MOUNTING	8-Pin Octal plug-in base, Panel Mounting Bracket			
POWER REQUIRE- MENTS	120 VAC, 50/60 Hz; (10%, -20%); 5WATT maxi- mum			
REPEAT ACCURACY	±.1% over rated voltages			
RESET TIME	100 mSEC minimum			
	Cycle Progress	3 Digit Green LED Display, seven segment numeric		
DISPLAY	Timing LED	Red LED blinks slowly (once per second) during timing; blinks rapidly after time out.		
MEMORY MX Models	EEPROM 100,000 read/write cycles			
HOUSING	1/16 DIN (48mm x 48mm) Housing			
WEIGHT	5oz (140g)	Shipping 1 lb.		

DIMENSIONS (INCHES/MILLIMETERS)

