

The ATC 365C is the latest generation in the popular long-ranger timer series. The microprocessor-based digital timer is equipped with three rotary knobs for setting and adjustment of the Preset. The Preset can be any three-digit value from .01 SEC to 999 HR. The Decimal and Range are switch selectable. The high-intensity blue vacuum fluorescent display is DIP switch selectable to Timeup or Timedown. Two heavy-duty 7A DPDT relays provide instantaneous, interval or delayed output control. Plug-in panel mounting allows easy replacement without the removal of field

COMPUTATION: Through its internal microcomputer, the 365B keeps track of the set point throughout the time cycle. Whenever there is a change in set point, even during a cycle, it instantly re-computes the time remaining and accurately determines time-out. This unique capability is especially valuable in the time-down modes as it allows you to shorten a cycle without loss of accuracy.

POSITIVE RESET TIME AND PULSE LENGTH: Digitally clocked by the microcomputer, the 365C's reset time is consistently of the same duration, regardless of variations in line voltage, power supply or time cycle. As a result, the 365C is not subject to false reset from momentary power interruptions (less than 30 mSEC). When the 365C operates in repeat-cycle mode, the output pulse is also digitally clocked so that both its occurrence and duration are consistent.

LONG-RANGER Times

WIDE RANGE: Each 365C Long-Ranger covers the overall span of 0.01 SEC to 999 HR, in nine

switch-selected ranges of 0 to 9.99,99.9 or 999 SEC, MIN or HR. The timer can be optimized within any selected range simply by removing appropriate selector knobs (e.g. with the timer in the 9.99 SEC range, you can obtain a tamper-proof span of 0.99 by setting the left selector at 0 and removing the knob).

PROGRAMMABLE DISPLAY: Depending on the position of an internal jumper, the 365C's three-digit cycle progress display will time UP to or DOWN from the set point; after time-out, it will either STOP or GO (i.e. display the time elapsed after time-out). To the right of the three-digit display, a timing bar "

"blinks once per second during the timing cycle and rapidly after timeout. At left, a marker "\(\neg ''\) turns on when the delayed relay is energized. The 365C is also available without display but with a pilot light that blinks once per second during the cycle and rapidly after time-out.


NOISE IMMUNITY: The 365C has formidable defenses against noise: transformer power supply, full-wave bridges, buffered logic. Furthermore its microcomputer detects; and rejects; noise pulses that manage to penetrate its defenses. No industrial timer has ever offered greater noise immunity.

RELIABILITY AND RUGGEDNESS: ATC firmly believes that no industrial timer has ever achieved a higher level of reliability and ruggedness. The 365C's electronic components have no moving parts and are assembled, virtually without hand wiring, from computer-tested circuit boards. Its few mechanical components have been selected for reliable service; the two load relays have a life expectancy of 100,000,000 operations and heavy-duty contacts rated at 7 amps; and the three rotary set point selector switches exhibit extremely low wear.

COMPACT, PLUG-IN AND DUST-TIGHT: Packaged in a 72mm² DIN housing, the 365C occupies 40% less panel space than conventional timers. It is a true plug-in timer that can be replaced in seconds without disturbing housing or wiring. The 365C is also fully gasketed and O-ring sealed to be dust and water-tight.

SELF DIAGNOSTICS: The time will display "FAIL" anytime there is a problem or the knobs are in between digits.

DIMENSIONS (INCHES/MILLIMETERS)



PANEL CUTOUT SHOWING DISTANCE BETWEEN ADJACENT CUTOUTS.

95-132 VAC, 50 or 60 Hz.

Running 0.06A at 120 VAC

Inrush — .3A.

120 VAC

	, 3	
240 VAC	90-264 VAC, 50 or 60 Hz. Inrush — .15A. Running — 0.03A at 240 VAC	
24 VAC	19.2-26.4 VAC, 50 or 60 Hz Inrush — 1A. Running — 0.25A at 24 VAC	
24 VDC	19.2-26.4 VDC, 5% ripple Running — .120A AT 24 VDC	
Number	one instantaneous and one delayed	
Туре	DPDT, Form C.	
Operate Time	P 13 mSEC, max.	
Release Time	10 mSEC, max.	
Contact Ratings	7A at 120, 240 or 24 VAC 1/6 HP	
Life	100 million operations (no load)	
± .001% ±.010 SEC of setting		
±.01% + .030 SEC of setting		
16 screw terminals accessible at rear		
72mm ² DIN size; plug-in design; fully gasketed, dust and water-tight in panel mounted installations.		
Standard	hardware is provided for front-of-panel mounting.	
Optional	Surface-mounting brackets with front-facing terminals.	
NEMA 12 molded case (1 timer)		
NET: AC 1 lb., 6 oz., DC 14 oz.	Shipping: AC 2 lbs. DC 1 lb., 8 oz.	
	24 VAC 24 VDC Number Type Operate Time Release Time Contact Ratings Life ± .001% ±.010 ±.01% + .030 \$ 16 screw termi 72mm² DIN size and water-tight Standard Optional NEMA 12 mold NET: AC 1 lb., 6	

SPECIFICATIONS Arrangement "30," with digital display available **MODELS** for On-Delay operation at 120, 240 or 24 VAC; and 24, 48 or 125 VDC Switch-selectable ranges of 0-9.99, **RANGES** 0-99.9 and 0-999 SEC, MIN or HR Single interval or delayed. **TIMING** Cycle **MODES** pulse-clocked at 50 to 80 mSEC (will Repeat Cycle be constant for a given unit) **RESET TIME** Clocked at 60 mSEC 3 digit display, 0.3 inch, high-intensity, blue programmable: DOWN and STOP, DOWN and DISPLAY GO, UP and STOP or UP and GO **CYCLE PROGRESS** ▼ display (left); energized at TIME-OUT time-out. display (right); blinks once per second during TIMING BAR cycle, rapidly after time-out. 120VAC 95-132VAC, 10mA max. current at Model 240VAC 190-264VAC, 10 mA max. current at 240V Model **CLOCK** 24VAC 19.2-26.4VAC, 20 mA max. current **INPUT** Model (terminal 15) 24VDC 19.2-26.4VDC (5% ripple), 5 mA **VOLTAGE** max. current at 24V Model **MODEL** 125 VDC

Model

125 VDC

32 to 140°F (0 to 60°C)

TEMPERATURE

RATING

19.2 to 26.4 VDC 50mA DC Max.

100 to 150 VDC 15mA DC

automatictiming.com

\\\WIRING		
Instantaneous Contacts 8 6 7 9 14 10 11 11 12 12 Start/Reset	L1 L2 5	Clock prewired display model. yed Contacts 13 11 12 D 2 D 2 IL JF
l o	3 12 11 10 9 8 7 0	

MODEL NUMBER >>>>> 365C		Р	
Range			
0 to 9.99, or 99.9 or 999 SEC, MIN, or HR 300			
Special 000			
Voltage & Frequency			
125 VDĆ	_		
24 VDC 1	1		
120 VAC 50-60 Hz	Į į		
=,,	1		
24 VAC, 50-60 Hz	-		
Special I			
Arrangeme			
With display, ON-delay/Time up or down and sto			
(reset on power failur			
Time up or down and g			
	tures		
Basic plug-i	า unit	P	
Stan	dard ι	ınit	Х
	Spe	cial	K
ACCESSORIES	•		
353-260-27-00: Surface Mounting Bracket Kit			
305-265-61-70: Retrofit Kit			

OPERATION

As soon as power is applied to terminals 1 & 2 of the timer, the instantaneous relay is energized and changes the states of its associated contacts (8-6-7 & 9-14-10). The timer then looks for terminal 15 (the clock terminal) to receive power. When terminal 15 is powered, the internal clock circuit is enabled and the timer starts to time. When the internal clock time equals the time set on the front face, the delayed relay energizes and changes the states of its associated contacts (3-4-5 & 13-11-12). The timer is reset by removing power from terminal 1 for at least 60 msec. At reset, both relays revert back to their shelf (without power) state.

SPECIAL NOTE FOR UNITS WITHOUT DISPLAYS: On non-display units, terminals 1 & 15 are jumpered together internally. As soon as power is applied, the instantaneous relay energizes and the timer starts to time immediately.

DISPLAY INFORMATION: The digital display can be set to operate in any of 4 modes by simply moving a jumper on the circuit board.

MODE:


- UP & STOP (30PX Time up to time set, transfer delayed relay, and stop timing).
- UP & GO (50PX Time up to time set, transfer delayed relay, and continue timing until unit is reset).
- DOWN & STOP (30PX Time down to zero from time set, transfer delayed relay, and stop timing).
- DOWN & GO (50PX Time down to zero from time set, transfer delayed relay, and continue timing up from zero giving a direct overshoot reading. Timing will continue until unit is reset). All 365C timers are shipped from the factory in the UP & STOP mode.

TYPICAL INSTALLATIONS

KEY SYMBOLS

PS P

POWER SUPPLY
CLOCK
INDEPENDENT LOADS



CONTACT
LOAD ENERGIZED
LOAD DE-ENERGIZED

All timers shown in "before start" position. Diagrams shown with power off unless otherwise marked.

Maximum load current through any load carrying contact is 7 amperes.

ON DELAY Reset on power failure.







INSTANTANEOUS CONTACTS

Contacts are transferred when power supply is energized, transferred back as shown when de-energized.


SUSTAINED START



MOMENTARY START



REPEAT CYCLE PULSE



Load A pulses on for approximately 50 mSEC.