

General Purpose Gauges - Contractor's Gauge

Standard features

- | | |
|--|---|
| <ul style="list-style-type: none"> • Wetted parts: Copper alloy • Window: Snap-in acrylic • Window ring: None • Dial: White aluminum | <ul style="list-style-type: none"> • Case fill: Not available • Accuracy: ±1% of span • Datasheet: 111.25CT |
|--|---|



Type	111.25CT	
Size	4½"	
Connection	LM	
Conn. size	¼" NPT	
Press scale ¹	PSI	PSI/KPA
30" Hg		
30"-0-15 psi	4277687	4277849
30"-0-30 psi	4277695	4277857
30"-0-60 psi	4277709	4277865
30"-0-100 psi	4277717	4277873
30"-0-160 psi	4277725	4277881
30"-0-200 psi	4277733	4277890
30"-0-300 psi	4277741	4277903
30"-0-400 psi		
15 psi	4277750	4277911
30 psi	4277768	4277920
60 psi	4277776	4277938
100 psi	4277784	4277946
160 psi	4277792	4277954
200 psi	4277806	4277962
300 psi	4277814	4277971
400 psi	4277822	4277989
600 psi	4277831	4277997

¹Vacuum scale: 30" Hg outside in black; 760 mm Hg inside in red.

Factory stocked items shown in **bold print**
 Items without part numbers are available - consult factory.