

PRODUCT FEATURES

- Full IEEE 802.3 and 1613 Compliance
- NEMA TS1/TS2 Compliance
- American Bureau of Shipping (ABS) Type Approval
- Sixteen (16) 10/100 BaseTX RJ-45 Ports
- -40° to 85°C Operating Temperature
- Auto Sensing 10/100BaseTX, Duplex, and MDIX
- Store-and-Forward Technology
- Up to 2.6 Gb/s Maximum Throughput
- Rugged Industrial DIN-Rail Enclosure
- Redundant Power Inputs (10-30 VDC)
- Bi-Color LEDs For Link, Speed, Activity & Duplex Status

Advanced Management Functions (With -A option only):

- IGMP Snooping
- VLAN
- QoS
- Trunking
- Mirroring
- N-View™ (Remote Monitoring Using OPC Technology)

PRODUCT OVERVIEW

The N-TRON® 516TX Series Industrial Ethernet Switch offers outstanding performance and ease of use. It is ideally suited for connecting Ethernet enabled industrial and/or security equipment and can be optionally configured with advanced Ethernet communication management functions.

Industrial Packaging and Specifications

The 516TX, designed to operate in industrial environments, is housed in a rugged DIN-rail-mounted steel enclosure. Optional panel and rack mount kits are also available. The switch comes standard with extended temperature rating, extended shock and vibration specs, redundant power inputs, and a high MTBF (greater than 2M hours).

Ease of Use

The 516TX requires no setup unless the advanced port functions are utilized. The sixteen 10/100BaseTX ports are auto sensing and auto configuring. Each port automatically negotiates for maximum speed and performance by default. Bi-color LEDs are provided to display the link status, link speed and activity of each port as well as power on/off status.

Performance

The 516TX supports up to 4,000 MAC addresses and uses advanced IEEE 802.3 Fast Ethernet 10/100BaseTX switching technology to eliminate network collisions and increase network determinism. A high-speed processor and backplane provide outstanding throughput performance.



ADVANCED MANAGEMENT FEATURES

The 516TX-A offers several management functions that can be easily configured using the COM Port (DB 9 connector located on the right side of the switch).

IGMP Snooping: Internet Group Management Protocol allows the N-Tron switch to intelligently forward and filter multicast traffic.

VLAN: Virtual Local Area Network allows switch segmentation in order to create two or more separate local area network domains.

QoS: Quality of Service streamlines network operation by managing packet priority. The primary goal of QoS is to improve the latency of prioritized Ethernet packets required for ring management, real-time and other interactive applications.

Trunking: Trunking (aggregation) enables multiple physical ports to be linked together and function as one uplink to another identically configured trunking-capable switch. This feature increases the bandwidth between switches and creates redundancy for applications requiring high levels of fault tolerant operation.

Port Mirroring: Port mirroring allows traffic on one port to be duplicated and sent to a designated mirror port. This function can be used to monitor Ethernet traffic on the designated source port using the assigned mirror port.

N-View OPC Switch Monitoring: (With -A or -N Option Only) N-View OPC server software can be used with popular HMI software packages to transmit operational information from N-View-capable switches. This technology enables network traffic monitoring, as well as alarm and trending details. In all, the N-View OPC Server collects 41 different traffic variables per port and five system level variables per switch, providing a complete overview of network load, service quality, and packet traffic. Empowered with N-View OPC Server data, users can resolve network problems faster and make more informed decisions about overall system performance.

516TX-A

Specifications

Switch Properties

Number of MAC Addresses:	4,000
Aging Time:	300s, Programmable (-A option)
Latency Typical:	2.1 μ s
Switching Method:	Store & Forward

Case Dimensions

Height:	2.3" (5.8 cm)
Width:	7.4" (18.8 cm)
Depth:	3.5" (8.8 cm)
Weight:	1.9 lbs (0.9 kg)
Din-Rail:	35 mm

Electrical

Redundant Input Voltage:	10-30 VDC
Input Current:	400 mA @ 24 VDC
Inrush:	7.0 amp/0.8ms @ 24 VDC
N-Tron Power Supply:	NTPS-24-1.3 (1.3A @ 24 VDC)

Environmental

Operating Temperature:	-40°C to 85°C
Storage Temperature:	-40°C to 85°C
Operating Humidity:	10% to 95% (Non Condensing)
Operating Altitude:	0 to 10,000 ft.

Shock and Vibration (bulkhead mounted)

Shock:	200 g @ 10 ms
Vibration/Seismic:	50 g, 5-200 Hz, Triaxial

Reliability

MTBF:	>2 Million Hours
-------	------------------

Serial Configuration Port

Com Parameters:	9600,n,8,1
-----------------	------------

Network Media

10BaseT:	\geq Cat3 Cable
100BaseTX:	\geq Cat5 Cable

Connectors

10/100BaseTX:	Sixteen (16) RJ-45 Copper Ports
---------------	---------------------------------

Recommended Wiring Clearance




Front:	2" (5.1 cm)
Side:	1" (2.6 cm)

Regulatory Approvals

FCC/CE (CFR 47, Part 15, Subpart B, Class A); ICES-003
EMC Dir 89/336/EEC, EN 50204, EN 55011
EN61000-4-2, 3, 4, 5, 6, 8, 11, EN61000-6-2, 4
ANSI C63.4
UL /cUL: Class I, Div 2, Groups A, B, C, D and T4
UL 508 and UL 1604
CAN/CSA-C22.2 No.213, ATEX II 3 G Ex nA
IEEE 1613 for Electric Utility Substations
ABS Type Approval for Shipboard Applications
GOST-R Certified, RoHS Compliant

Designed to comply with:
NEMA TS1/TS2 for Traffic Control





516TX

ORDERING INFORMATION

PART NUMBER	DESCRIPTION
516TX-A.....	16-port 10/100BaseTX, Industrial Ethernet Switch, DIN-Rail with Advanced Management Features (includes N-View)
516TX-N.....	16-port 10/100BaseTX, Industrial Ethernet Switch, DIN-Rail with N-View OPC switch monitoring
516TX.....	16-port 10/100BaseTX, Industrial Ethernet Switch, DIN-Rail
NTPS-24-1.3.....	N-Tron Power Supply (1.3 amp @ 24 VDC)
900-PM.....	Panel Mount Kit - converts switch mounting from DIN-rail to panel mount
URMK.....	Universal Rack Mount Kit

N-TRON USA & Corporate Headquarters
3101 International Blvd. Building 6
Mobile, AL 36606 • USA
Phone +1-251-342-2164
Fax +1-251-342-6353
www.n-tron.com

please visit us worldwide at www.n-tron.com

© 2012 N-Tron Corporation. N-Tron and the N-Tron logo are trademarks of N-Tron Corporation. Product names mentioned herein are for identification purposes only and may be trademarks and/or registered trademarks of their respective company. Specifications subject to change without notice. The responsibility for the use and application of N-Tron products rests with the end user. N-Tron makes no warranties as to the fitness or suitability of any N-Tron product for any specific application. N-Tron Corporation shall not be liable for any damage resulting from the installation, use, or misuse of this product. Printed in USA. REV 2012.11.13

QUALITY MANAGEMENT SYSTEM
CERTIFIED BY DNV
== ISO 9001:2008 ==