



■ Features :

- Constant current mode design
- Universal AC input / Full range
- Protections:Short circuit / Over voltage
- Fully isolated plastic case
- Small and compact size
- Cooling by free air convection
- $^{\bullet}$ Class $\scriptstyle \rm II$ power unit, no FG
- Class 2 power unit
- Pass LPS
- IP30 design
- Suitable for LED lighting and moving sign applications
- 100% full load burn-in test
- Low cost / High reliability
- 2 years warranty

SPECIFICATION



SPECIFICATION MODEL		APC-16-350	APC-16-700	
WIODEL	RATED CURRENT	350mA	700mA	
ОИТРИТ		12~48V	9~24V	
	DC VOLTAGE RANGE RATED POWER	12~48V	16.8W	
			250mVp-p	
	RIPPLE & NOISE (max.) Note.2		250111Vp-p	
	VOLTAGE TOLERANCE Note.3 CURRENT ACCURACY	±8.0%		
	LINE REGULATION	±1.0%		
	LOAD REGULATION	±3.0%		
	SETUP, RISE TIME	3000ms, 200ms / 230VAC 3000ms, 200ms / 115VAC at full load		
	•	20ms/230VAC 12ms/115VAC at full load		
	HOLD UP TIME (Typ.)			
INPUT	VOLTAGE RANGE Note.4 FREQUENCY RANGE	90 ~ 264VAC 127 ~ 370VDC 47 ~ 63Hz		
		84%	83%	
	EFFICIENCY(Typ.) AC CURRENT		83%	
	INRUSH CURRENT(Typ.)	0.3A/230VAC;0.5A/115VAC COLD START 45A(twidth=210µs measured at 50% Ipeak) at 230VAC		
	LEAKAGE CURRENT	0.25mA / 240VAC		
	LEARAGE CURRENT		27.6~ 33.5V	
PROTECTION	OVER VOLTAGE	50.4~ 60V Protection type: Shut off o/p voltage, clamping by zener diode	27.0~ 33.30	
ENVIRONMENT	WORKING TEMP.	-30 ~ 70°C (Refer to "Derating Curve")		
	WORKING HUMIDITY	20 ~ 90% RH non-condensing		
	STORAGE TEMP., HUMIDITY	-40 ~ +80°C, 10 ~ 95% RH		
	TEMP. COEFFICIENT	±0.2%/°C (0~50°C)		
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, period for 60min. each along X, Y, Z axes		
SAFETY & EMC (Note 5)	SAFETY STANDARDS	UL8750, CSA C22.2 No.250.0-08 approved, Design refer to TUV EN61347-1		
	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC		
	ISOLATION RESISTANCE	I/P-O/P:>100M Ohms / 500VDC / 25°C / 70% RH		
	EMC EMISSION	Compliance to EN55015,EN61000-3-2 Class A,EN61000-3-3		
	EMC IMMUNITY	Compliance to EN61547,EN61000-4-2,3,4,5,6,8,11; light industry level(surge 2KV), criteria A		
OTHERS	MTBF	1145.7K hrs min. MIL-HDBK-217F (25°C)		
	DIMENSION	77*40*29(L*W*H)		
	PACKING	0.1Kg; 120pcs/14Kg/0.93CUFT		
NOTE	Ripple & noise are measure Tolerance : includes set up Derating may be needed ur The power supply is consided complete installation, the fin	ally mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. red at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. p tolerance, line regulation and load regulation. under low input voltage. Please check the static characteristic for more details. dered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the inal equipment manufacturers must re-qualify EMC Directive on the complete installation again. able for lighting applications in EU countries. Please check with your local authorities for the possible use of the unit.		



