



The gripping strength of spiral wrap tubing is enhanced by both its torsional cut and its rigid profile. It retains its strength under repeated flexing and bending and follows wire paths easily, which yields neat, free-running cable bundles. It is extremely useful on long continuous runs where many leads are required; wires can enter or break out at any point. Spiral wrap can be removed easily for troubleshooting and then re-applied.

SWP - POLYETHYLENE

Conforms to A-A-59602

Catalog Number Size	Nominal O.D. inches mm	Nominal Wall Thickness inches mm	Nominal Pitch inches mm	Maximum Bundle Size* inches mm	Colors**	Std. Spools*** ft / spool
SWP-1/8	0.125 3.18	0.031 0.79	0.250 6.35	0.5 12.7	Nat., Blk.	100, 500
SWP-3/16	0.188 4.76	0.031 0.79	0.250 6.35	1.5 38.1	Nat., Blk.	100, 500
SWP-1/4XXT	0.250 6.35	0.031 0.79	0.375 9.53	2.0 50.8	Nat., Blk.	100, 500
SWP-1/4XT	0.250 6.35	0.040 1.02	0.375 9.53	2.0 50.8	Nat., Blk.	100, 500
SWP-1/4	0.250 6.35	0.058 1.47	0.313 7.94	2.0 50.8	Nat., Blk.	100, 500
SWP-3/8	0.375 9.53	0.058 1.47	0.438 11.11	3.0 76.2	Nat., Blk.	100, 500
SWP-1/2	0.500 12.70	0.058 1.47	0.563 14.29	4.0 101.6	Nat., Blk.	100, 250
SWP-5/8	0.625 15.88	0.062 1.57	0.875 22.23	5.0 127.0	Nat., Blk.	50, 100 (Box)
SWP-3/4	0.750 19.05	0.065 1.65	0.875 22.23	6.0 152.4	Nat., Blk.	50, 100 (Box)
SWP-1"	1.000 25.40	0.100 2.54	0.875 22.23	8.0 203.2	Nat., Blk.	50, 100 (Box)

SWN - NYLON

Conforms to: A - A - 59602, MIL - T - 47287A

Catalog Number Size	Nominal O.D. inches mm	Nominal Wall Thickness inches mm	Nominal Pitch inches mm	Maximum Bundle Size* inches mm	Colors**	Std. Spools*** ft / spool
SWN-1/8	0.125 3.18	0.016 0.41	0.250 6.35	0.5 12.7	Nat., Blk.	100, 500
SWN-1/4	0.250 6.35	0.030 0.76	0.313 7.94	2.0 50.8	Nat., Blk.	100, 500
SWN-3/8	0.375 9.53	0.030 0.76	0.438 11.11	3.0 76.2	Nat., Blk.	100, 500
SWN-1/2	0.500 12.70	0.030 0.76	0.563 14.29	4.0 101.6	Nat., Blk.	100, 250
SWN-3/4	0.750 19.05	0.040 1.02	0.875 22.23	6.0 152.4	Nat., Blk.	50, 100 (Box)
SWN-1"	1.000 25.40	0.040 1.02	1.000 25.40	8.0 203.2	Nat., Blk.	50, 100 (Box)

SWT - PTFE

Conforms to: A - A - 59602, MIL - T - 47287A, MIL - I - 22129B, AMS 3651B, 3653

Catalog Number Size	Nominal O.D. inches mm	Nominal Wall Thickness inches mm	Nominal Pitch inches mm	Maximum Bundle Size* inches mm	Colors**	Std. Spools*** ft / spool
SWT-1/8XXT	0.125 3.18	0.016 0.41	0.250 6.35	0.5 12.7	Natural	25, 100
SWT-1/8XT	0.125 3.18	0.020 0.51	0.250 6.35	0.5 12.7	Natural	50, 100
SWT-1/8	0.125 3.18	0.030 0.76	0.250 6.35	0.5 12.7	Natural	50, 100
SWT-3/16	0.188 4.76	0.030 0.76	0.250 6.35	1.0 25.4	Natural	25, 100
SWT-1/4XXT	0.250 6.35	0.015 0.38	0.375 9.53	2.0 50.8	Natural	25, 100
SWT-1/4XT	0.250 6.35	0.020 0.51	0.375 9.53	2.0 50.8	Natural	50, 100
SWT-1/4	0.250 6.35	0.030 0.76	0.375 9.53	2.0 50.8	Natural	50, 100
SWT-3/8	0.375 9.53	0.030 0.76	0.438 11.11	2.5 63.5	Natural	25, 100
SWT-1/2	0.500 12.70	0.030 0.76	0.563 14.29	3.0 76.2	Natural	25, 100
SWT-3/4	0.750 19.05	0.040 1.02	0.875 22.23	4.0 101.6	Natural	25, 100 (Box)
SWT-1"	1.000 25.40	0.040 1.02	1.000 24.50	6.0 152.4	Natural	25, 100 (Box)

* Size will vary on a specific bundle depending on desired flexibility and protection

** ADDITIONAL COLORS AVAILABLE ON REQUEST

*** Occasional random lengths