

Type 12 Wiring Trough 1486 Series

Application

- Designed to enclose and protect multiple wiring junctions from dirt, dust, oil and water.

Standards

- UL 870 Type 1
- CSA Type 1
- Complies with
 - NEMA Type 12
 - JIC EGP-1-1967
 - JIC EMP-1-1967
 - IEC 60529, IP54




Construction

- Formed 14 gauge steel.
- Smooth continuously welded seams.
- Butt hinged cover is secured with easily operated screw clamps.
- Oil resistant gaskets are permanently secured.
- 12 gauge external mounting feet are welded to the back.

Finish

- Troughs and covers are finished in ANSI 61 gray powder coating.



Part No.	Overall Dimensions			Cover Size					Ship Wt. (lbs)
	A	B	C	D	E	F	G	H	

Part No.	Overall Dimensions			Cover Size						Ship Wt. (lbs)
	A	B	C	D	E	F	G	H	J	
1486B12	2.50	2.50	12.00	12.31	2.84	2.00	2.00	3.19	6.00	3
1486B18	2.50	2.50	18.00	18.31	2.84	2.00	2.00	3.19	12.00	5
1486B24	2.50	2.50	24.00	24.31	2.84	2.00	3.00	3.19	9.00	6
1486B30	2.50	2.50	30.00	30.31	2.84	3.00	3.00	3.19	12.00	9
1486B36	2.50	2.50	36.00	36.31	2.84	3.00	3.00	3.19	15.00	10
1486B48	2.50	2.50	48.00	48.31	2.84	3.00	3.00	3.19	21.00	13
1486B60	2.50	2.50	60.00	60.31	2.84	3.00	4.00	3.19	18.00	16
1486B72	2.50	2.50	72.00	72.31	2.84	3.00	4.00	3.19	22.00	19
1486C12	4.00	4.00	12.00	12.31	4.34	2.00	2.00	4.69	6.00	6
1486C18	4.00	4.00	18.00	18.31	4.34	2.00	2.00	4.69	12.00	8
1486C24	4.00	4.00	24.00	24.31	4.34	2.00	3.00	4.69	9.00	10
1486C30	4.00	4.00	30.00	30.31	4.34	3.00	3.00	4.69	12.00	13
1486C36	4.00	4.00	36.00	36.31	4.34	3.00	3.00	4.69	15.00	16
1486C48	4.00	4.00	48.00	48.31	4.34	3.00	3.00	4.69	21.00	20
1486C60	4.00	4.00	60.00	60.31	4.34	3.00	4.00	4.69	18.00	25
1486C72	4.00	4.00	72.00	72.31	4.34	3.00	4.00	4.69	22.00	30
1486D12	6.00	6.00	12.00	12.31	6.34	2.00	2.00	6.69	6.00	9
1486D18	6.00	6.00	18.00	18.31	6.34	2.00	2.00	6.69	12.00	16
1486D24	6.00	6.00	24.00	24.31	6.34	2.00	3.00	6.69	9.00	16
1486D30	6.00	6.00	30.00	30.31	6.34	3.00	3.00	6.69	12.00	19
1486D36	6.00	6.00	36.00	36.31	6.34	3.00	3.00	6.69	15.00	23
1486D48	6.00	6.00	48.00	48.31	6.34	3.00	3.00	6.69	21.00	29
1486D60	6.00	6.00	60.00	60.31	6.34	3.00	4.00	6.69	18.00	32
1486D72	6.00	6.00	72.00	72.31	6.34	3.00	4.00	6.69	22.00	43

Data subject to change without notice