
FEMALE END VIEW		SPECIFICATIONS			
		CONTACT CARRIER MATERIAL	TPU		
		MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW		
		CONTACT MATERIAL/PLATING	BRASS/GOLD		
		COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL		
		RATED CURRENT [A]	9.0 A		
		RATED VOLTAGE [V]	600 V		
1		OUTER JACKET MATERIAL/COLOR	PVC/YELLOW		
		CONDUCTOR INSULATION MATERIAL	PVC		
1 = GREEN/YELLOW 2 = BROWN		NUMBER OF CONDUCTORS [AWG]	3x18 AWG		
3 = BLUE		TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)		
		PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67		
test.					



CABLE LENGTH	TOLERANCE		
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER TOLERANCE		
STRIP LENGTH			
0-7mm	±0.5mm		
8-29mm	±1.0mm		
30-49mm	±2.0mm		
50-69mm	±3.0mm		
70–100mm	±4.0mm		
OVER 100mm	±5.0mm		

RDS

ΒY

SOURCE DRAWING - FOR REFERENCE ONLY

DRDER			RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology Sensors and Automation Controls		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1–800–544–7769 (763) 553–7300 (763) 553–0708 fax turck.com	
			MATERIAL		DRFT JBJ APVD	DATE 03/11/03 SCALE 1=1.0	DESCRIPTION RKM 3	0-*M	
			SEE SPECIFICATIONS		UNIT OF MEASUREMENT		IDENTIFICATION NO.		REV
-	06/06/12	39016	FINISH	CONTACT TURCK FOR MORE	MILLIMETE	ER [INCH]			D
>	D6/06/12 DATE	59016 ECO NO.	SEE SPECIFICATIONS	INFORMATION	DO NOT SCALE	THIS DRAWING	FILE: 777001915	SHEET	1 OF 1

NOTES:

REV DESCRIPTION

UPDATE VOLTAGE RATING

D

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.