






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	6/15/10	D.GRIFFIN
B	ECN 4859: REVISED SERIES MICRO B MOLDED HOOD	6/23/10	D.FRISIELLO
C	ECN 5868: ADDED LENGTHS 03 M, 075 M, REVISED WIRE MAP	12/7/11	D.FRISIELLO
D	ECN5915: REVISED VIEWS OF USB MICRO B MALE	01/10/12	DFP



1X TWISTED PAIR 28AWG STRANDED TINNED COPPER
 2X 28 AWG STRANDED TINNED COPPER,
 OVERALL ALUMINIZED POLYESTER SHIELD,
 STRANDED TINNED COPPER DRAIN WIRE,
 TINNED COPPER BRAID SHIELD
 PVC JACKET, BLACK

MODEL NUMBER	LENGTH METERS [FEET]
CSMUAMICB-03M	0.3 [.98]
CSMUAMICB-05M	0.5 [1.64]
CSMUAMICB-075M	0.75 [2.46]
CSMUAMICB-1M	1.0 [3.28]
CSMUAMICB-2M	2.0 [6.56]
CSMUAMICB-3M	3.0 [9.84]



NOTES:

1. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.
3. CABLE ASSEMBLY SHALL HAVE 360° SHIELD TERMINATION
4. DRAIN WIRE CONNECTED TO CONNECTOR SHELLS.
5. CABLE ASSEMBLY MUST MEET REQUIREMENTS OF USB 2.0

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM	06/03/2010		CATEGORY
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 .XX = ±.02 .XXX = ±.005	CHECKED BY D. CASTRO	06/03/2010	PRODUCT DESCRIPTION	
PROJECTION	APPROVED BY S. SMITH	06/03/2010	CA, USB A - M/ MINI-B 5-POS M	
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CSMUAMICB	REV. D
			SCALE: NONE	CAD FILE: CSMUAMICB.SLDDRW
				SHEET 1 OF 1