




DPDT Non-Latching Electromechanical Relay Signal Integrity up to 18Gbps



SURFACE MOUNT HIGH REPEATABILITY, BROADBAND TO-5 RELAYS DPDT



SERIES	RELAY TYPE
SRF300	Repeatable, RF relay
SRF300D	Repeatable, RF relay with internal diode for coil transient suppression
SRF300DD	Repeatable, RF relay with internal diodes for coil transient suppression and polarity reversal protection
SRF303	Sensitive, repeatable, RF relay
SRF303D	Sensitive, repeatable, RF relay with internal diode for coil transient suppression
SRF303DD	Sensitive, repeatable, RF relay with internal diodes for coil transient suppression and polarity reversal protection

DESCRIPTION

The ultraminiature SRF300 and SRF303 relays are designed to provide a practical surface-mount solution with improved RF signal repeatability over the frequency range. These relays are engineered for use in RF attenuator, RF switch matrices, ATE and other applications that require dependable high frequency signal fidelity and performance.

The SRF300 and SRF303 feature:

- High repeatability
- Broader bandwidth
- Metal enclosure for EMI shielding
- High isolation between control and signal paths
- · High resistance to ESD


The following unique construction features and manufacturing techniques provide excellent robustness to environmental

extremes and overall high reliability:

- Uniframe motor design provides high magnetic efficiency and mechanical rigidity
- Minimum mass components and welded construction provide maximum resistance to shock and vibration
- Advanced cleaning techniques provide maximum assurance of internal cleanliness
- Hermetically sealed
- Solder Dipped Leads, (RoHS compliant solder option available)

The Series SRF300D/SRF303D and SRF300DD/SRF303DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. This hybrid package reduces required PC board floor space byreducing the number of external components needed to drive the relay.

ENVIRONMENTAL AND PHYSICAL SPECIFICATIONS						
Temperature	Storage	–65°C to +125°C				
(Ambient)	Operating	–55°C to +85°C				
Vibration (General Note	I)	10 g's to 500 Hz				
Shock (General Note	l)	30 g's, 6ms half sine				
Enclosure		Hermetically sealed				
Woight	SRF300	0.09 oz. (2.55g) max.				
Weight	SRF303	0.16 oz. (4.5g) max.				




SRF300/SRF303 Page 1 SRF300SRF303\102012\Q3



TELEDYNE RELAYS Everywhereyoulook[™]

DPDT Non-Latching Electromechanical Relay Signal Integrity up to 18Gbps





DPDT Non-Latching Electromechanical Relay Signal Integrity up to 18Gbps


SERIES SRF300/SRF303 GENERAL ELECTRICAL SPECIFICATIONS (@25°C)						
Contact Arrangement	2 Form C (DPDT)					
Rated Duty	Continuous					
Contact Resistance	0.15 Ω max.					
Contact Load Rating	Resistive: 1Amp/28Vdc Low level: 10 to 50 μA @ 10 to 50 mV					
Contact Life Ratings	10,000,000 cycles (typical) at low level					
Coil Operating Rower	SRF300-5: 500 mW @ nominal coil		SRF300-12: 370 mW @ nominal coil			
Coil Operating Power	SRF303-5: 250 mW @ nominal coil		SRF303-12: 169 mW @ nominal coil			
Operate Time SRF300: 4.0 mS max. SRF303: 6.0 mS max.						
Release Time	SRF300: 3.0 mS max.	SRF300D, SRF300DD: 4.0 mS max.				
Release Time	SRF303: 3.0 mS max.	SR	SRF303D, SRF303DD: 7.5 mS max.			
Intercontact Capacitance	0.4 pf typical					
Insulation Resistance	1,000 M Ω min. between mutually isolated terminals					
Dielectric Strength	350 Vrms (60 Hz) @ atmospheric pressure					
Negative Coil Transient (Vdc)	SRF300D/SRF303D, SRF300DD/SRF303DD		1.0 max			
Diode P.I.V. (Vdc)	SRF300D/SRF303D, SRF300DD/SRF303DD		100 min.			

DETAILED ELECTRICAL SPECIFICATIONS (@25°C)

BASE PART NUMBERS (SI SRF300DD)	RF300, SRF300D,	SRF300-5 SRF300D-5 SRF300DD-5	SRF300-12 SRF300D-12 SRF300DD-12
Coil Voltage, Nominal (Vdc)		5.0	12.0
Coil Posistanco (Ohms	SRF300, SRF300D	50	390
Coil Resistance (Ohms ±20%)	SRF300DD (General Note II)	39	390
Coil Current (mAdc@ 25	Min.	93.2	25.6
°C)(RF300DD Series)	Max.	128.2	32.8
Pick-up Voltage (Vdc	SRF300, SRF300D,	3.6	9.0
max.)	SRF300DD	3.9	10.0

BASE PART NUMBERS (S SRF303DD)	RF303, SRF303D,	SRF303-5 SRF303D-5 SRF303DD-5	SRF303-12 SRF303D-12 SRF303DD-12
Coil Voltage, Nominal (Vdc)		5.0	12.0
Coil Resistance (Ohms	SRF303, SRF303D	100	850
±20%)	SRF303DD (General Note II)	64	850
Coil Current (mAdc@ 25	Min.	56.8	11.7
°C)(RF303DD Series)	Max.	78.1	15.0
Pick-up Voltage (Vdc	SRF303, SRF303D,	3.6	9.0
max.)	SRF303DD	3.7	11.0


DPDT Non-Latching Electromechanical Relay Signal Integrity up to 18Gbps



TELEDYNE

RELAYS

DPDT Non-Latching Electromechanical Relay Signal Integrity up to 18Gbps



2³¹ - 1 PRBS signal

TELEDYNE

RELAYS

- PRBS output of 300 mV $_{\rm P-P}$ (nominal) RF PCB effect (negligible) not removed from measurement
- Data shown is typical of both poles



DPDT Non-Latching Electromechanical Relay Signal Integrity up to 18Gbps

