



## Industrial Adhesives & Tapes

- Products
- Applications
- Industries
- Capabilities
- Support

[United States](#) > [All 3M Products](#) > [Market Segments](#) > [Manufacturing and Industry](#) > [Industrial Adhesives & Tapes](#) > [Industrial Adhesives & Tapes](#) > [Non-Structural Adhesives](#) > [Spray Adhesives](#) > 3M™ Multi-Purpose 27 Spray Adhesive Clear, 20 fl oz can, net weight 13.05 oz, 12 cans per case

# 3M™ Multi-Purpose 27 Spray Adhesive Clear, 20 fl oz can, net weight 13.05 oz, 12 cans per case

UPC# 00051111078327 3M Product Number 27 3M Product Number 27-Spray-Adhesive 3M ID 62490649209



3M™ Multi-Purpose 27 Spray Adhesive is a versatile, economical, industrial grade, mist spray aerosol adhesive.

- Fast tack
- Lightweight applications
- Mist spray pattern
- General Industrial
- Bonding, attaching, adhering, fastening, securing, gluing, tacking, sticking, gripping and hanging

### Overview

### Support

Ideal for bonding paper, cardboard, fabrics, soft foams and many other lightweight materials.

### Specifications

<b>Application</b>	Spray
<b>Method</b>	
<b>Bonding Range (One Surface)</b>	15 seconds to 10 minutes
<b>Brand</b>	3M
<b>Can Size</b>	20 Fluid Ounce (US)
<b>Capabilities</b>	Sustainability
<b>Color</b>	Clear
<b>Environmental Considerations</b>	California Air Resources Board, Helps contribute to LEED® credits, Ozone Transport Commission
<b>Flammability</b>	Flammable
<b>Heat Resistance</b>	<170 Degree Fahrenheit

<b>Industry - Use</b>	General Industrial, MRO
<b>Net Weight</b>	13.05 Ounce
<b>Product Form</b>	Can
<b>Size</b>	Aerosol
<b>Solids Weight Percent (Approximate)</b>	21 Percent
<b>Strength Requirements</b>	Low Strength
<b>Substrate 2</b>	EPDM Rubber, Fabric, Felt, Cork & Fibrous Glass, Flexible Foam (Latex, Urethane), Glass & Ceramics, Leather, Metal, Paper & Cardboard, Plastics (ABS, PVC, Acrylic), Plastics (Flexible Vinyl), Plastics (High Performance Nylon), Plastics (Polyolefins and Thermoplastic Elastomers), Rigid Foam (Urethane), Rubber (Except EPDM), Wood & Hardboard
<b>Units per Case</b>	12
<b>Volatile Organic Compounds (VOCs)</b>	59 Percent