


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	5/2/01	DFP
B	ECN 3063: ADDED NOTES TO DWG, ROTATED RJ12 JACK 180 DEG.	10/30/07	D.CASTRO
C	ECN 7419: CN RELEASE, REVISED MATL, FORMAT, ROHS	5/22/14	D.FRISIELLO
D	ECN 7677: CHANGE REAR JACK HOUSING FROM PC/ABS TO ABS	11/12/14	D.FRISIELLO



**NOTES:**

**MATERIAL:**

PLUG HOUSING: POLYCARBONATE, CLEAR, UL94V-0  
 JACK HOUSING, FRONT: ABS, IVORY, PANTONE 7501C.  
 JACK HOUSING, REAR: ABS, IVORY, PANTONE 7501C.  
 CONTACTS: PHOSPHOR BRONZE  
 CABLE JACKET: PVC, IVORY

**FINISH:**

CONTACTS: GOLD PLATING IN CONTACT AREA  
 OVER NICKEL PLATE OVERALL.

**CABLE CHARACTERISTICS:**

6 CONDUCTOR FLAT MODULAR CORD,  
 U.L. STYLE 20251, 26 AWG STRANDED (7X34)

**MISCELLANEOUS:**

PLUG CONFORMS TO TIA-1096  
 OPERATING TEMPERATURE RANGE: -20°C TO +60°C  
 EXTENSION CABLES TO BE TESTED FOR CONTINUITY  
 EXTENSION CABLES TO BE INDIVIDUALLY PACKAGED IN  
 ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

**REGULATORY COMPLIANCE:**

CE2011/65/EU(RoHS DIRECTIVE)

WIRING MAP	
"J1"	"P1"
1	1
2	2
3	3
4	4
5	5
6	6

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D PARHAM	4/17/2001		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [5.1] .XXX = ±.005 [1.3]	CHECKED BY T CLARK	4/24/2001	CATEGORY TELECOM/MODULAR	
	APPROVED BY R CARRICK	4/26/2001	PRODUCT DESCRIPTION EXTENDER, (6X6)M/F STRAIGHT	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>
REF	REF	REF	DWG. NO. TAC535-6-7	REV. <b>D</b>
SCALE: NONE			CAD FILE: TAC535-6-7.SLDDRW	
			SHEET 1 OF 1	