



### 3120



Basic Part Number	Length A
3120-1	.205
3120-2	.250

**3120-X-00-XX-00-00-08-0**  
Swage mount in .034 mounting hole

### 3122 ⇒ 3153




Basic Part Number	Pin Length A
3153-X	.180
3141-X	.230
3122-X	.280
3149-X	.380
3123-X	.580
3140-X	.780
3124-X	.880

- X -	Board Thickness	Length V
1	.031	.051
2	.062	.082

**31XX-X-00-XX-00-00-08-0**  
Swage mount in .043 hole

### 3101 ⇒ 3106




Basic Part Number	Pin Length A
3101-X	.150
3102-X	.188
3103-X	.300
3104-X	.500
3105-X	.750
3106-X	1.000

- X -	Board Thickness	Length V
1	.031	.051
2	.062	.082
3	.094	.113

**310X-X-00-XX-00-00-08-0**  
Swage mount in .043 hole

### 3221 ⇒ 3223




Basic Part Number	Pin Length A
3221-X	.100
3222-X	.150
3223-X	.300

- X -	Board Thickness	Length V
1	.031	.051
2	.062	.082
3	.094	.113

**322X-X-00-XX-00-00-08-0**  
Swage mount in .043 hole

### 3125/3126




Basic Part Number	Pin Length S
3125-X	.170
3126-X	.420

- X -	Board Thickness	Length V
1	.031	.051
2	.062	.082
3	.094	.113


**312X-X-00-XX-00-00-08-0**  
Swage mount in .043 hole

### 0995



**0995-0-00-XX-00-00-03-0**  
Press-fit in .057 mounting hole

### 4526



**4526-0-00-XX-00-00-03-0**  
Press-fit in .040 mounting hole

#### SPECIFICATIONS

**PIN MATERIAL:**  
Brass Alloy 360, 1/2 Hard  
( Except Swage pins which are annealed )

**DIMENSION IN INCHES**  
**TOLERANCES ON:**  
LENGTHS: ±.005  
DIAMETERS: ±.002  
ANGLES: ± 2°

**ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - XX - 0**

**BASIC PART #**

**SPECIFY PIN FINISH:**

- 01 200µ" TIN/LEAD OVER NICKEL
- ◇ 80 200µ" TIN OVER NICKEL (RoHS)
- ◇ 15 10µ" GOLD OVER NICKEL (RoHS)
- ◇ 21 20µ" GOLD OVER NICKEL (RoHS)
- ◇ 34 50µ" GOLD OVER NICKEL (RoHS)

