

Continuous Flex

SD 200

Continuous flex halogen-free polyurethane data cable with extreme temperature range



BRÖCKSKES · D-VIERSEN · SD 200 25 x 0.14 mm² CE



Marking for SD 200 7742501:

SAB BRÖCKSKES · D-VIERSEN · SD 200 25 x 0.14 mm² CE

B
34

Construction:

Conductor:	bare copper strands, extra fine wires
Insulation:	TPE
Color code:	DIN 47100, see page O/26
Stranding:	specialy adjusted layering with non-woven tape over each layer
Wrapping:	non-woven tape
Jacket material:	PUR, TPU acc. to EN50363-10-2 + VDE 0207-363-10-2 with matte surface
Jacket color:	grayish tan (RAL 7032)

Outstanding features:



- free from paint wetting impairment substances (PWIS-free)
- flexible at low temperatures
- halogen-free
- travel > 10 m is possible
- high abrasion resistance
- minimal bending radius
- small outer diameter

Technical data:

Peak operating voltage:	max. 350 V acc. to VDE 0812
Testing voltage:	conductor/conductor: 1500 V
Min. bending radius: <i>continuously flexing:</i>	7.5 x O.D.
Radiation resistance:	1 x 10 ⁷ cJ/kg
Temperature range: <i>static:</i> <i>flexing:</i>	DIN VDE -50/+90°C -40/+90°C
Halogen-free:	acc. to IEC 60754-1 + VDE 0482-754-1
Oil resistance:	very good - TPU acc. to EN 50363-10-2 + VDE 0207-363-10-2
Chemical resistance:	good against acids, alkalines, solvents, hydraulic liquids, etc.
Continuous flexibility	very good
Weather resistance:	very good
Approvals:	CE, EAC, RoHS
Absence of harmful substances:	acc. to RoHS directive of the European Union see page O/30

item no.	no. of conductors incl. ground	nominal outer-ø inch	mm	cable weight ≈lbs/mft
▶ 26 AWG (≈ 18/38) ▪ 0.14 mm²				
7740201	2	0.122	3.1	8
7740301	3	0.130	3.3	10
7740401	4	0.146	3.7	13
7740501	5	0.161	4.1	16
7740701	7	0.185	4.7	22
7741001	10	0.217	5.5	28
7741201	12	0.224	5.7	32
7741401	14	0.232	5.9	36
7741801	18	0.268	6.8	48
7742501	25	0.319	8.1	63
7743201	32	0.350	8.9	81

item no.	no. of conductors incl. ground	nominal outer-ø inch	mm	cable weight ≈lbs/mft
▶ 24 AWG (≈ 32/38) ▪ 0.25 mm²				
7740202	2	0.130	3.3	11
7740302	3	0.146	3.7	13
7740402	4	0.157	4.0	15
7740502	5	0.169	4.3	20
7740702	7	0.197	5.0	26
7741002	10	0.217	5.5	34
7741202	12	0.232	5.9	40
7741402	14	0.240	6.1	46
7741802	18	0.268	6.8	59
7742502	25	0.319	8.1	82
7743202	32	0.350	8.9	104

item no.	no. of conductors incl. ground	nominal outer-ø inch	mm	cable weight ≈lbs/mft
▶ 22 AWG (≈ 42/38) ▪ 0.34 mm²				
7740203	2	0.146	3.7	11
7740303	3	0.154	3.9	14
7740403	4	0.165	4.2	17
7740503	5	0.177	4.5	20
7740703	7	0.205	5.2	28
7741003	10	0.240	6.1	35
7741203	12	0.248	6.3	40
7741403	14	0.260	6.6	46
7741803	18	0.287	7.3	59
7742503	25	0.350	8.9	82
7743203	32	0.374	9.5	104

Other dimensions and colors are available on request



Possible on request:

- 20 AWG or 19 AWG

