

LAMB ELECTRIC

Model: 116420-13 116420-32*

DESCRIPTION

- Two stage
- 240 volts
- 5.7"/145 mm diameter
- Double ball bearings
- Single speed
- Tangential bypass discharge
- Thermoset fan end bracket


POW

- Aluminum commutator bracket

DESIGN APPLICATION

- Equipment operating in environments requiring separation of working air from motor ventilating air

- Designed to handle clean, dry, filtered air only



SPECIAL FEATURES

- Suitable for 240 volt AC operation, 50/60 Hz

- UL recognized, category PRGY2 (E47185)

- Skeleton-frame design

- Epoxy painted fan case


- Patented air seal bearing construction, U.S. Patent

#4.088.424

- The Lamb Electric vacuum motor line offers a wide range of performance levels to meet design needs

*Model 116420-32 has fan shell inlet tube 1.875" diameter x 1.0" long.

TYPICAL MOTOR PERFORMANCE.*									(At 240 volts, 60Hz, test data is corrected to standard conditions of 29.92 Hg, 68° F.)															
	100 - 90 -						-		/ac						120			Orifice (Inches)	Amps	Watts (In)	RPM	Vac (In.H2O)	Flow (CFM)	Air Watts
							1-	♦ — F	low					•	100			2.000	4.7	1060	18623	4.2	106.8	53
	80 -										×							1.750	4.7	1061	18623	7.0	105.4	87
Α	- 70 -				ľ				~	×					- 80			1.500	4.7	1062	18623	11.8	99.3	138
S	g 60 -															CFM		1.250	4.7	1058	18623	20.3	90.4	216
т	- 50 -						┣	/							60	Flow		1.125	4.6	1053	18675	26.3	83.2	257
М	ling 40 -						×	Ì,	\leftarrow							Air F		1.000	4.6	1045	18792	33.6	74.0	293
	× 30 -					×									40			0.875	4.5	1028	18967	42.3	63.4	315
D	20 -				×													0.750	4.3	986	19324	50.7	50.8	303
Α	10 -			×											- 20			0.625	4.1	934	20012	59.0	38.0	263
т	0	~	×												0			0.500	3.8	870	20854	67.2	25.8	204
Α	0 -	00	50	75	00	25	50	75	000.	25	50	500	50	00	+ 0			0.375	3.5	805	21885	75.3	15.5	137
		0.000	0.250	0.37	0.500	0.625	0.750	0.87	-		1.2	1.5	1.750	2.000				0.250	3.2	746	22859	82.9	7.5	73
						C	Drifice [Diamete	er (Inch	es)								0.000	3.0	697	23806	92.1	0.0	0




Orifice	Amps	Watts	RPM	Vac	Flow	Air	
(mm)		(In)		(mm H2O)	(L/Sec)	Watts	
48.0	4.7	1060	18623	138	50.1	68	
40.0	4.7	1062	18623	263	47.7	123	
30.0	4.6	1055	18652	599	40.8	239	
23.0	4.5	1032	18923	1019	31.2	310	
19.0	4.3	985	19338	1292	23.9	302	
16.0	4.1	936	19984	1490	18.2	265	
13.0	3.8	876	20770	1686	12.8	210	
10.0	3.5	815	21730	1882	8.0	147	
6.5	3.2	749	22810	2096	3.7	76	
0.0	3.0	697	23806	2339	0.0	0	

Note: Metric performance data is calculated from the ASTM data above.

* Data represents performance of a typical motor sampled from a large production quantity. Individual motor data may vary due to normal manufacturing variations.

Test Specs: 240 volts Minimum Sealed Vacuum: 82.0" ORIFICE: 13 mm Minimum Vacuum: 60.0" Maximum Watts: 975

PRODUCT BULLETIN



WARNING - When using AMETEK Lamb Electric bypass motors in machines that come in contact with foam, liquid (including water), or other foreign substances, the machine must be designed and constructed to prevent those substances from reaching the fan system, motor housing, and electrical components. Lamb Electric vacuum motors other than hazardous duty models should not be applied in machines that come in contact with dry chemicals or other volatile materials. Failure to observe these precautions could cause flashing (depending on volatility) or electrical shock which could result in property damage and severe bodily injury, including death in extreme cases. All applications incorporating Lamb Electric motors should be submitted to appropriate organizations or agencies for testing specifically related to the safety of your equipment.

AMETEK/Lamb Electric Division 627 Lake Street Kent, Ohio 44240 U.S.A. Tel: (330) 673-3451 Fax: (330) 673-8994 Ametek GmbH P. O. Box 1251 D-71667 Marbach Germany Phone: + 49-714-484-9512 Fax: + 49-714-484-9513 AMETEK/Singapore Private Limited 10 Ang Mo Kio Street 65 # 05-12 Techpoint Singapore 2056 Tel: + 65-484-2388 Fax: + 65-481-6588

Issued: March, 1998